

## EMH 575 W/SE/75

EMH (Classic Line) | Economical short-arc metal halide lamps



### Areas of application

- Clubs
- Shops
- Small stages

### Product benefits

- Effective high-quality light at an attractive price
- Economical versions of the most popular metal halide lamps
- Powerful and durable
- High quality for which the name of OSRAM is widely famous
- Excellent price/performance ratio
- Available in different wattages and color temperatures
- Available in single-ended and double-ended versions



## Product datasheet

### Technical data


#### Electrical data

Nominal wattage	575.00 W
Nominal voltage	97.5 V
Nominal current	7.00 A

#### Photometrical data

Color temperature	7200 K
Color rendering index Ra	> 70

#### Dimensions & weight



Length	125.0 mm
Light center length (LCL)	65.0 mm
Diameter	28.0 mm

#### Lifespan

Lifespan	750 h
----------	-------

#### Additional product data

Base (standard designation)	GX9.5
-----------------------------	-------

#### Capabilities

Burning position	Any
------------------	-----

#### Certificates & standards

EEI – Energy Label	B
--------------------	---

## Product datasheet

---

### Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation EMH lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. More information is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321345080	EMH 575 W/SE/75	Folding carton box 1	156 mm x 51 mm x 79 mm	0.63 dm <sup>3</sup>	119.00 g
4008321345097	EMH 575 W/SE/75	Shipping carton box 10	276 mm x 221 mm x 194 mm	11.83 dm <sup>3</sup>	1594.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### References / Links

Further technical information on EMH lamps and information for manufacturers of operating equipment can be requested directly from OSRAM.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---