

Silicon carbide composite bench stones

Type 9010

LAPPORT
SCHLEIFTECHNIK

Application:

Grinding and honing stones for heavy-duty and high-quality steels, also for carbide-tipped tools or solid carbide tools.

Execution:

- Can be used with oil, petroleum, water or even dry
- Ceramic bond
- One side rough, the other side fine

Advantage:

- For consistent hardness and grip, machined on all sides after burning
- Very high grinding force
- Especially non-slip



Art. no.	69321 030
Brand	LAPPORT
Manufacturer Part Number	101040
Length x width x thickness	125 x 50 x 20 mm
Number of pieces per packet	1 PCS
Binding	Ceramically bound
Width	50 mm
Thickness	20 mm
Form	Rectangular
Suitable for finishing	2 - suitable
Suitable for main machining	1 - very suitable
Suitable for surface inspection	3 - less suitable
Suitable for surface care	3 - less suitable
Suitable for material rubber	2 - suitable
Suitable for material cast iron	1 - very suitable
Suitable for material HSS	2 - suitable
Suitable for material carbide	2 - suitable
Suitable for material ceramic	2 - suitable
Suitable for material plastics	2 - suitable
Suitable for material non-ferrous metals	1 - very suitable
Suitable for material steel (hardened)	3 - less suitable
Suitable for material steel (unhardened)	3 - less suitable
Suitable for material tool steel	3 - less suitable
ISO	525
Length	125 mm
Length x width	125 x 50 mm
Type description	Silicon carbide
Gross Weight	0.211 kg
Product Group	6HL