

## **SPECIFICATION**

Part No. : **DBP.433.T.A.30** 

Description : Dielectric Band Pass Filter for 433MHz

Bandwidth 2MHz

Features : Center Frequency 433.92MHz

Supports ISM 433.05MHz to 434.79MHz use.

Low Insertion Loss

Low Pass-Band Ripple

High Ultimate Attenuation

Dims: 10\*7.5\*3.7mm







#### 1. Introduction

Taoglas are utilizing their deep understanding of the RF component design and manufacturing process to provide high-quality, small-form-factor, cost-effective and easy to implement RF filters. The Taoglas Filters Division will feature a range of off-the-shelf filters for a variety of applications, including filters for emerging license free bands used for IoT and for GPS L1/L2 and L1/L5 applications. We can also work with customers to develop bespoke filter solutions.

Taoglas dielectric filters are designed to be used in wireless transmitters or receivers. These filters are designed to protect the LNA from noisy out of band emissions originated from nearby transmitters that can overdrive, or even damage your LNA. Overdriving the LNA results in non-linear distortion which negatively impacts the sensitivity of your receiver.

By selecting the proper Taoglas filter you can eliminate unnecessary out of band noise while maintaining minimal in-band insertion loss. The filter is manufactured as a single ceramic block [monoblock] which provides high reliability, low insertion loss and high attenuation in a simple compact SMD package.

The DBP.433.T.A.30 is a standard Taoglas product but can be customized for specific customer needs. For more information please contact your regional sales office.




# 2. Specification

ELECTRICAL				
Centre Frequency (Fo)	433.92MHz			
3dB Bandwidth	10MHz			
Insertion Loss	3.0 dB max			
Passband Ripple	0.5 dB max			
Return Loss	< -10 dB			
Attenuation	> 45.0 dB @ 0 ~ 390 MHz			
	> 17.0 dB @ 390 MHz ~ 410 MHz			
	> 14.0 dB @ 468 MHz ~ 480 MHz			
	> 20.0 dB @ 480 MHz ~1 GHz			
In/Out Impedance	<b>50</b> Ω			
Power Dissipation	1.0 W min.			
MECHANICAL				
Dimension	10 x 7.5 x 3.7 (L x W x H)			
Material	Ceramic			
Finish	Ag plated			
ENVIRONMENTAL				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-40°C to 85°C			
Moisture Senseitvity Level (MSL)	3 (168 Hours)			




## 3. Characteristics Curve

#### 3.1. Pass Band Return & Insertion Loss




#### 3.2. Out-Of-Band Attenuation





## 4. Mechanical Drawings (Unit: mm)

## 4.1. Antenna Drawing






# 4.2. Recommended PCB Layout 4.2.1. Top Copper

Pads 1 and 2 should be connected to a 50 ohm transmission line.


Pads 3, 4, 5 and 6 are connected to GND.

Pads 1 and 2 are the same size. Pads 3, 4, 5 and 6 are the same size.



#### 4.2.2. Top Solder Paste

Pads 1 and 2 are the same size. Pads 3, 4, 5 and 6 are the same size.



#### NOTE:

- 1. Ag Plated area
- 2. Solder Mask area
- 3. Copper area
- 4. Paste area
- 5. Copper Keepout Area




- 6. Any vias in pads should be either filled or tented to prevent solder from wicking away from the pad during reflow.
- 7. The dimension tolerances should follow standard PCB manufacturing quidelines




## 4.2.3. Top Solder Mask

Pads 1 and 2 are the same size. Pads 3, 4, 5 and 6 are the same size. This drawing is a negative of solder mask. Black regions are anti-mask.



#### 4.2.4. Composite Diagram



#### NOTE:


- 1. Ag Plated area
- 2. Solder Mask area
- 3. Copper area
- 4. Paste area
- 5. Copper Keepout Area




- 6. Any vias in pads should be either filled or tented to prevent solder from wicking away from the pad during reflow.
- 7. The dimension tolerances should follow standard PCB manufacturing guidelines



#### 4.3. Evaluation Board






NOTE: 1.All material must be RoHS compliant.

	Name	Material	Finish	aTY
1	Filter	Ceramic	Clear	1
2	PCB	Composite 1.0t	Black	1
3	SMA(F) ST	Brass	Au Plated	2




# **5. Recommended Reflow Soldering Profile**

Phase	Profile Features	Maximum
Preheat	Temperature Min Temperature Max	150 °C 180 °C
Ramp-Up	Duration Avg. Ramp up rate	60-120 sec 3 °C/sec (max)
Reflow	Temperature Duration	220 °C 30-40 sec
Peak	Temperature Duration	265 °C 5 sec Max
Ramp Down	Avg. Ramp down rate	3 °C/sec (max)






# 6. Recommended Reflow Soldering Profile







2500 pc DBP.433.T.A.30 2 reel in small inner box Dimensions - 340\*340\*51 Weight - 4.17Kg



4 inner boxes / 10000 pcs in one carton Carton Dimensions - 210\*345\*360mm Weight -17.2Kg



Pallet Dimensions 1100\*1100\*1280mm 24 Cartons per Pallet 6 Cartons per layer 4 Layers





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.