




Inductive high-temperature sensor

IIA3015ZBPKG/5M/SH



Product characteristics

Electrical design		PNP
Output function		normally open
Sensing range	[mm]	15
Housing		threaded type
Dimensions	[mm]	M30 x 1.5 / L = 79

Application

Application		high-temperature applications
-------------	--	-------------------------------

Electrical data

Operating voltage	[V]	10...35 DC
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection		yes

Outputs

Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	150
Switching frequency DC	[Hz]	200
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Sensing range	[mm]	15
Operating distance	[mm]	0...12.1

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.6 / brass: 0.3 / aluminium: 0.2 / copper: 0.1
Hysteresis	[% of Sr]	3...15
Switch point drift	[% of Sr]	-10...10

II5930



Inductive high-temperature sensor

IIA3015ZBPKG/5M/SH

Operating conditions

Ambient temperature	[°C]	0...180
Protection		IP 65

Tests / approvals

EMC	EN 61000-4-2 ESD	2 kV CD / 4 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
MTTF	[years]	174

Mechanical data

Weight	[g]	357
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 79
Thread designation		M30 x 1.5
Materials		housing: stainless steel; sensing face: LCP

Accessories

Accessories (supplied)	lock nuts: 2
------------------------	--------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 5 m, silicone; highly flexible; 3 x 0.34 mm²

Connection



Core colours :

- BK = black
- BN = brown
- BU = blue