

## Screw tap, HSSE Ultra HL M ISO 2X (6HX) 0° 371 B

for universal use up to 1000 N/mm<sup>2</sup>

**ATORN**<sup>®</sup>



### Application

For producing metric threads on CNC machines or conventional machines in **through holes** in steel, stainless steel, non-ferrous metals, cast iron and special alloys up to 1200 N/mm<sup>2</sup>.

### Advantage

- ideal for long service life requirements and materials that are difficult to machine, such as stainless steel
- Innovative cutting geometry and ULTRA HL coating guarantee high process reliability even under difficult machining conditions

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	18	12	8	11	10	19	19	17	19	17	18	13		18	7	6	6		

<b>Art. No.</b>	<b>13250 300</b>
<b>Type</b>	UNI MAX 45HL Control
<b>Thread type</b>	Metric thread
<b>Thread type x nominal diameter</b>	M10
<b>Pitch</b>	1.5 mm
<b>Hole type</b>	Clearance hole ≤ 3xD
<b>Cutting material</b>	HSSE
<b>Surface</b>	ULTRA HL
<b>Lead angle shape</b>	B
<b>Tolerance of screw taps</b>	ISO 2X (6HX)
<b>Twist angle</b>	0°
<b>Shaft diameter</b>	10 mm
<b>Application type/machine type</b>	CNC, Conventional
<b>Core hole diameter</b>	8.5 mm
<b>Coolant supply</b>	External
<b>Length</b>	100 mm
<b>Shank square</b>	8 mm
<b>Cutting speed (steel 1000) suitability</b>	1
<b>Cutting speed (steel 1300) suitability</b>	2
<b>Overall stainless steel suitability</b>	1
<b>fitness not iron total</b>	1
<b>fitness Titan/Nickel/Super total</b>	1
<b>Cutting speed (cast) suitability</b>	1
<b>Cutting speed (hard 55) suitability</b>	3
<b>Cutting speed (hard 65) suitability</b>	3
<b>DIN</b>	371

### EAN-Code

4050293578805