



# PCB TERMINAL BLOCKS

## 5.08mm Pitch High Power Rising Clamp Terminal Blocks


- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 pole solid block
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.2-4.0mm<sup>2</sup> (30-12AWG) solid cable
- 0.2-2.5mm<sup>2</sup> (30-12AWG) stranded cable
- Guided pin alignment
- Captive screw
-  approved

CTB0708



TYPE NO.	POLES	LENGTH
CTB0708/2	2	10.16mm
CTB0708/3	3	15.24mm
CTB0708/4	4	20.32mm
CTB0708/5	5	25.4mm
CTB0708/6	6	30.48mm
CTB0708/7	7	35.56mm
CTB0708/8	8	40.64mm
CTB0708/9	9	45.72mm
CTB0708/10	10	50.8mm
CTB0708/11	11	55.88mm
CTB0708/12	12	60.96mm

SPECIFICATION	
Rating	24A/320V UL=16A/300V, VDE&IMQ=24A/450V
Dielectric strength	≥2.5kV
Impulse withstand voltage	4kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Tinned, nickel plated brass
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.5mm



PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDs &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS

RELAY  
BASES

DIN RAIL  
ENCLOSURES

BATTERIES

SOLAR  
PANELS

TRANS-  
FORMERS



+44 (0)1638 716101  
info@camdenboss.com  
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.1

