

ET 200PRO ERSE/RSSE HF ELECTRONIC REVERSING STARTER ELECTRONIC (SOFT) SWITCHING FULL MOTOR PROTECTION COMPRISING: ELECTRONIC OVERLOAD PROTECTION + THERMISTOR 3 AC 400V/0.9KW; 0.9A...2.00A; BRAKE CONTACT AC 400V; 4DI HAN Q4/2 - HAN Q8/0

General technical data:		
product brand name		SIRIUS
Product designation		ET 200pro motor starters
Design of the product		reversing starter
Product function		
• Bus communication		Yes
• direct start		No
• reverse starting		Yes
• on-site operation		Yes
• Short circuit protection		Yes
Design of the switching contact		solid-state / thyristor / 2 phases
Product component Motor brake output		Yes
Trip class		CLASS 5, 10, 20 and 30 adjustable
Type of assignment		1
Product feature		
• brake control with 400 V AC		Yes
• brake control with 230 V AC		No
• brake control with 24 V DC		No
• brake control with 180 V DC		No
• brake control with 500 V DC		No
Type of voltage of the supply voltage for brake control required		AC
Supply voltage for brake control required	V	400
Surge voltage resistance Rated value	kV	6

maximum permissible voltage for safe isolation between main and auxiliary circuit	V	400
Equipment marking acc. to DIN EN 61346-2		Q
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		A
Mounting type		screw fixing
Depth	mm	150
Height	mm	230
Width	mm	110

#### Main circuit:

Operating voltage Rated value	V	400 ... 500
Adjustable response value current of the current-dependent overload release	A	0.15 ... 2
Operating current at AC-3 at 400 V Rated value	A	2
Operating power at AC-3 at 400 V Rated value	W	900
Operating power for three-phase motors at 400 V at 50 Hz minimum	W	700
Operating power for three-phase motors at 400 V at 50 Hz maximum	W	5 500
Maximum short-circuit current breaking capacity (I <sub>cu</sub> ) at 400 V Rated value	A	100 000
Design of short-circuit protection		fuse
Number of poles for main current circuit		3
Type of the motor protection		full motor protection
Mechanical service life (switching cycles) of the main contacts typical		30 000 000

#### Control circuit/ Control:

Type of voltage of the control supply voltage		DC
Control supply voltage 1 for DC Final rated value	V	24
Control supply voltage 1 for DC Rated value		
• minimum permissible	V	20.4
• maximum permissible	V	28.8

#### Supply voltage:

Type of voltage of the supply voltage		DC
Supply voltage 1 for DC Final rated value	V	24
Supply voltage 1 for DC Rated value		
• minimum permissible	V	20.4
• maximum permissible	V	28.8

#### Ambient conditions:

Protection class IP		IP65
Ambient temperature		
• during operation	°C	-25 ... +55

• during storage	°C	-40 ... +70
• during transport	°C	-40 ... +70
Relative humidity during operation	%	5 ... 95
<b>Vibration resistance</b>		2g
<b>Shock resistance</b>		15g / 11 ms
<b>Degree of pollution</b>		3
<b>Installation altitude at height above sea level maximum</b>	m	3 500
<b>mounting position</b>		vertical, horizontal

#### Communication/ Protocol:

<b>Protocol is supported</b>		
• PROFIBUS DP protocol		Yes
• PROFINET protocol		Yes
• AS-interface protocol		No
<b>Design of the interface PROFINET protocol</b>		Yes
<b>Type of electrical connection of the communication interface</b>		via backplane bus

#### Connections/ Terminals:

<b>Number of digital inputs</b>		4
<b>Number of sockets</b>		
• for digital input signals		4
• for digital output signals		0
<b>Product function</b>		
• digital inputs parameterizable		Yes
• digital outputs parameterizable		No
<b>Type of electrical connection</b>		
• 1 for digital input signals		M12 socket
• 2 for digital input signals		M12 socket
• 3 for digital input signals		M12 socket
• 4 for digital input signals		M12 socket
<b>Type of electrical connection</b>		
• at the manufacturer-specific device interface		optical interface
• for main energy infeed		socket according to ISO23570
• for load-side outgoing feeder		socket according to ISO23570
• for main energy transmission		socket according to ISO23570
• for supply voltage infeed		via backplane bus
• for supply voltage transmission		via backplane bus
• for main current circuit		tab terminals

#### Certificate of suitability

<b>Protection against electrical shock</b>		finger-safe
--	--	-------------

#### Certificates/ approvals:



**Test  
Certificates**

**other**

[Type Test  
Certificates/Test  
Report](#)

[Environmental  
Confirmations](#)

Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RK13045KS703AA3>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RK13045KS703AA3/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK13045KS703AA3&lang=en>



last modified:

09.03.2015