

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **2162701063**
Status: **Active**
Overview: Off-the-Shelf Cable Assemblies
Description: SL Female-to-SL Female Off-the-Shelf (OTS) Cable Assembly, Positive Lock, Single Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Black

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	<u>216270</u>
Application	Signal, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SL-to-SL
Overview	<u>Off-the-Shelf Cable Assemblies</u>
Product Name	SL
Type	Discrete Wire Assembly
UPC	193264730773

Physical

Cable Length	300.00mm
Circuits (Loaded)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	10.717/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.63mm max.
Wire Size AWG	22
Wire/Cable Type	UL 11028


Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	600V AC/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2162701060-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)

1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
Terphenyl,
hydrogenated
2-(2H-benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
sodium
peroxometaborate
2,4-di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p
2-benzotriazol-2-
yl-4,6-di-tert-
butylphenol
Ammonium-
pentadecafluorooctanoate
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
1,3-propanesultone
1-vinylimidazole
1,2-diethoxyethane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
dodecamethylcyclohexasiloxane

China RoHS

Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
di-n-pentyl phthalate
(DPP)
furan
4-o-tolylazo-o-
toluidine
ethylene thiourea
4-methyl-m-
phenylenediamine
o-toluidine
butyl 4-
hydroxybenzoate
phenanthrene
dicyclohexyl phthalate
p-(1,1-
dimethylpropyl)phenol
N-methylacetamide
dimethyl sulphate
pentacosafuorotridecanoic
acid
Perfluorohexane-1-
sulphonic acid and its
salts
5-sec-butyl-2-(2,4-
dimethylcyclohex-3-
en-1-yl)-5
1,2-
benzenedicarboxylic
acid, di-C6-10-alkyl
est
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Cadmium sulphate
Bisphenol-A
Methylhexahydrophthalic
anhydride
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
Reaction
products of 1,3,4-
thiadiazolidine-2,5-d
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Pyrene
Perfluorobutane
sulfonic acid (PFBS)
and its sal
Tris(4-nonylphenyl,
branched and linear)
phosphi
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
4-Nonylphenol,
branched and linear,
ethoxylated
Trixylyl phosphate
4-Nonylphenol,
branched and linear
[substances w
Zirconia
Aluminosilicate

Refractory Ceramic
Fibr
Aluminosilicate
Refractory Ceramic
Fibres
Sodium dichromate
4,4'-Oxydianiline and
its salts
Boric acid
Disodium tetraborate
n-pentyl-
isopentylphthalate
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
2-benzyl-2-
dimethylamino-4-
morpholinobutyropheno
2-methyl-1-(4-
methylthiophenyl)-2-
morpholinoprop
1,2-
benzenedicarboxylic
acid, dipentylester,
bra
benzo[a]pyrene
1,2-
benzenedicarboxylic
acid; di-C6-8-
branched a
1,2,3-trichloropropane
N-methyl-2-
pyrrolidone
1,2-
benzenedicarboxylic
acid; di-C7-11-
branched
2-ethoxyethyl acetate
Cobalt sulphate
Cobalt-dinitrate
Carbonic acid,
cobalt(2+) salt (1:1)
2-methoxyethanol
2-ethoxyethanol
trichloroethylene
Boric acid, disodium
salt, hydrate
potassium dichromate
potassium chromate
Pitch, coal tar, high-
temp.; Pitch
Lead chromate
molybdate sulfate red
lead chromate
Anthracene oil,
anthracene-low;
Anthracene Oil F
lead hydrogen
arsenate
bis(tributyltin) oxide
alkanes, C10-13,
chloro
bis(2-ethylhexyl)
phthalate (DEHP)
musk xylene

diarsenic trioxide
diarsenic pentaoxide
Cobalt-dichloride
dibutyl phthalate
(DBP)
4,4'-
diaminodiphenylmethane
potassium
hydroxyoctaoxodizincatedichromate(1-)
Fatty acids, C16-18,
lead salts
[phthalato(2-)]dioxotrilead
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
Sulfurous acid, lead
salt, dibasic
Borate(1-),
tetrafluoro-, lead (2+)
dioxobis(stearato)trilead
tetralead trioxide
sulphate
Lead-titanium-trioxide
lead oxide sulfate
Silicic acid, lead salt
lead dinitrate
cadmium
lead
[4-[[4-anilino-1-
naphthyl]]4-
(dimethylamino)phen
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(
Lead oxide
trilead bis(carbonate)
dihydroxide
orange lead
cadmium oxide (non-
pyrophoric)
Diboron-trioxide
cadmium carbonate
N,N,N',N'-
tetramethyl-4,4'-
methylenedianiline
2,2'-dichloro-4,4'-
methylenedianiline
dichromium
tris(chromate)
bis(2-methoxyethyl)
phthalate
pentazinc chromate
octahydroxide
trilead diarsenate
arsenic acid

**Halogen-Free
Status**

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
216270 Series

This document was generated on 11/03/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION