


**Data sheet | Item number: 879-3020**

Energy consumption meter; for direct connection; 65A; 3x230/400V; 50Hz;  
MID; Modbus® & M-Bus; 2 x S0 interface; 4PS




[www.wago.com/879-3020](http://www.wago.com/879-3020)



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.



Conductor cross-section	Primary rated current	Ambient operating temperature		
		40 °C	55 °C	70 °C
4 mm <sup>2</sup> (Fine-stranded conductor)	15 A			X
	25 A		X	
	30 A	X		
4 mm <sup>2</sup> (Fine-stranded conductor; with insulated ferrule)	17 A			X
	27 A		X	
	32 A	X		
6 mm <sup>2</sup> (Fine-stranded conductor)	25 A			X
	37 A		X	
	41 A	X		
6 mm <sup>2</sup> (Fine-stranded conductor; with insulated ferrule)	27 A			X
	39 A		X	
	41 A	X		
10 mm <sup>2</sup> (Fine-stranded conductor)	30 A			X
	40 A		X	
	55 A	X		
10 mm <sup>2</sup> (Fine-stranded conductor; with insulated ferrule)	30 A			X
	45 A		X	
	55 A	X		
16 mm <sup>2</sup> (Fine-stranded conductor)	35 A			X
	50 A		X	
	65 A	X		
16 mm <sup>2</sup> (Fine-stranded conductor; with insulated ferrule)	35 A			X
	55 A		X	
	65 A	X		
25 mm <sup>2</sup> (Fine-stranded conductor)	65 A			X
	45 A		X	

## Item description

### Short description:

Comprehensive energy measurement is necessary for optimizing energy consumption. WAGO now has new energy meters in its portfolio that simplify this task while providing several key advantages. They use the push-in connection technology with a lever, making them connect quickly and easily. The devices have a width of just 72 mm for direct measurement. These widths save a tremendous amount of control cabinet space. In addition to the values for active and reactive energy, the energy meters also record the mains frequency as well as current, voltage and power for all phases. And the user can conveniently see all of these energy characteristics at a glance on a large, illuminated display.

### Features:

- Saving time at every level thanks to the Push-in CAGE CLAMP<sup>®</sup> and lever
- Real space savings: 72 mm wide (4PS)
- Measurement of delivery and purchase
- Energy recording via 4 rates
- The communications pro: M-Bus and Modbus<sup>®</sup> interface and 2 SO pulse outputs
- Full transparency at a glance: Display energy quality characteristics on an illuminated full-format display
- Intuitive configuration: Touch-sensitive controls and configuration app via Bluetooth<sup>®</sup>

Subject to changes. Please also observe the further product documentation!



## Data

### Technical data

### Configuration

Configuration options	Touch-sensitive controls Configuration app via Bluetooth®
-----------------------	--

### Input

Input signal type	Voltage Current
Network configuration	Two-wire, three-wire and four-wire networks
Nominal input voltage $U_{i\text{nom}}$	3 x (3) x AC 230 ... 400 V
Input voltage range	±20 %
Reference current $I_{\text{ref}}$	5 A
Input current $I_i$	≤ 65 A
Frequency range	45 ... 65 Hz

### Communication

Communication	Modbus® M-Bus Bluetooth®
Interface	RS-485 (2-wire); 2x S0 interfaces (configurable)
Rate control input	AC/DC 230 V
Indicators	LCD with backlight

### Signal processing

Measured variables (calculated)	Active and reactive energy in supply and reference direction
Messungsart (Lastgang)	No

### Measurement error

Accuracy class	Class B (= 1 % error); Active energy per EN 50470-3
Calibration validity period	8 years

Subject to changes. Please also observe the further product documentation!



## Supply

Power supply type	Via measurement circuit
Power consumption $P_{\max}$ (phase; effective power)	2 W
Power consumption $P_{\max}$ (phase; apparent power)	10 VA

## Safety and protection

Dielectric strength	4 kV; 1 min
Impulse withstand voltage (1.2/50 $\mu$ s)	6 kV
Pollution degree	2
Protection type	IP51 (front side); IP20 (connection)
Protection class	II

## Connection data

Connection type (1)	Voltage/current
Connection technology	Push-in CAGE CLAMP®
WAGO Connector	WAGO 2616 Series
Actuation type	Lever
Solid conductor	0.75 ... 16 mm <sup>2</sup> / 18 ... 4 AWG
Fine-stranded conductor	0.75 ... 25 mm <sup>2</sup> / 18 ... 4 AWG
Fine-stranded conductor; with insulated ferrule	0.75 ... 16 mm <sup>2</sup>
Fine-stranded conductor; with uninsulated ferrule	0.75 ... 16 mm <sup>2</sup>
Strip length	18 ... 20 mm / 0.71 ... 0.79 inch
Connection type 2	Communication/rate control input
Connection technology 2	Push-in CAGE CLAMP®
WAGO Connector 2	WAGO 857 Series
Actuation type 2	Lever
Solid conductor 2	0.2 ... 4 mm <sup>2</sup> / 24 ... 12 AWG
Fine-stranded conductor 2	0.2 ... 4 mm <sup>2</sup> / 24 ... 12 AWG
Fine-stranded conductor; with insulated ferrule 2	0.25 ... 2.5 mm <sup>2</sup> /
Fine-stranded conductor; with uninsulated ferrule 2	0.25 ... 2.5 mm <sup>2</sup> /
Strip length 2	9 ... 11 mm / 0.35 ... 0.43 inch

## Physical data

Width	72 mm / 2.835 inch
-------	--------------------

Subject to changes. Please also observe the further product documentation!



Height	140 mm / 5.512 inch
Depth	63 mm / 2.48 inch
Note (dimensions)	Height without cover: 92 mm

**Mechanical data**

Mounting type	DIN-35 rail
---------------	-------------

**Material data**

Housing material	PC 940A
Weight	280 g

**Environmental requirements**

Surrounding air temperature (operation)	-40 ... 70 °C
Relative humidity	75% (during storage 95 %)

**Standards and specifications**

Conformity marking	CE
Standards/Specifications	EN 50470-1/3 MID-compliant

**Commercial data**

PU (SPU)	1 Stück
Country of origin	CN
GTIN	4055144071399
Customs tariff number	90283019000

**Downloads****Documentation****Manual**

WAGO Energy Meters (MID) 4PS / 4PU	V 1.1 25 May 2021	pdf 3.1 MB	Download
---------------------------------------	----------------------	---------------	----------

**Instruction Leaflet**

Energy consumption meter	V 1.12 2 Mar 2021	pdf 915.0 kB	Download
--------------------------	----------------------	-----------------	----------

Subject to changes. Please also observe the further product documentation!



## CAD/CAE-Data

### CAD data

2D/3D Models 879-3020	<a href="#">URL</a>	<a href="#">Download</a>
-----------------------	---------------------	--------------------------

---

### CAE data

ZUKEN Portal 879-3020	<a href="#">URL</a>	<a href="#">Download</a>
-----------------------	---------------------	--------------------------

---

## Environmental Product Compliance

### Compliance Search

Environmental Product Compliance 879-3020	<a href="#">URL</a>	<a href="#">Download</a>
---	---------------------	--------------------------

Energy consumption meter; for direct connection; 65A; 3x230/400V; 50Hz; MID;  
Modbus® & M-Bus; 2 x S0 interface; 4PS

---

## Installation Notes

Subject to changes. Please also observe the further product documentation!