



Figure similar

POWER SUPPLY; PHASES:3; PN(KW):0,72;  
 UPRI(V):400+/-20; USEC(V DC):24; ISEC(A DC):30/36  
 (60/40 CEL); F(HZ):50...60; VECTOR GR./SHIELD  
 WNG.:YD1 /0; PROTECTION CL.:I; TA/ISOKL:60 /B;  
 W(%):4,2; IP00; TYPE OF TERMINALS:SCREW  
 CONNECTION; INSTALLATION:SCREW; EN 61558-2-  
 6, EN61131-2 >SAFETY ISOLATING  
 TRANSFORMER<

### General technical data:

<b>Product designation</b>		<a href="#">4AV3300-2EB00-0A</a>
<b>product brand name</b>		SIDAC
<b>Vector group</b>		li0
<b>Certificate of suitability</b>		CE
<b>Product function</b>		
<ul style="list-style-type: none"> <li>• Temperature monitoring</li> </ul>		No
<ul style="list-style-type: none"> <li>• Insulation monitoring</li> </ul>		No
<ul style="list-style-type: none"> <li>• Short-circuit and overload proof</li> </ul>		No
<ul style="list-style-type: none"> <li>• varistor protective wiring</li> </ul>		Yes
<b>Operating resource protection class</b>		I
<b>Number of shielding windings</b>		0

### Inputs:

<b>Phase number of the inputs</b>		3
<b>Type of current of the inputs</b>		AC
<b>Input voltage</b>		
<ul style="list-style-type: none"> <li>• _1 Rated value</li> </ul>	V	420
<ul style="list-style-type: none"> <li>• _2 Rated value</li> </ul>	V	400
<ul style="list-style-type: none"> <li>• _3 Rated value</li> </ul>	V	380
<b>Electrical input frequency</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	Hz	50
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	Hz	60
<b>Input voltage</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	V	342

• maximum	V	445.2
Type of electrical connection at input for main current circuit		screw-type terminals

#### Outputs:

Type of current		DC
• _1 at output		
Output voltage		
• _1 Rated value	V	24
Output voltage of the measurement signal at analog output for DC maximum	V	28.8
Output voltage of the measurement signal at analog output for DC minimum	V	20.4
Output current		
• _1 Rated value	A	30
Type of electrical connection at output for main current circuit		screw-type terminals
Relative residual ripple		
• of the output voltage 1 for main current circuit maximum	%	5

#### Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	60
Protection class IP		IP00

#### Mechanical data:

Mounting type		screws
Construction form of the iron core		3UI 90/50
Width	m	216
Height	m	220
Depth	m	158

#### Certificates/ approvals:

General Product Approval	Shipping Approval	other
--------------------------	-------------------	-------



[Declaration of Conformity](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4AV33002EB000A>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4AV33002EB000A>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AV33002EB000A&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AV33002EB000A&lang=en)

**last modified:**

16.03.2015