

Electronic dial gauge

ID-N

Mitutoyo

Application:

for measuring lengths and differences in length, e.g. concentricity, flatness, position measurements.

Version:

- Preset function
- Counting direction can be switched
- ABSOLUTE system for reliable measurement
- LCD digit size 6.2 mm
- Digimatic
- Hold button
- ON/OFF
- IP66

Advantage:

- Graphic display in the event that tolerance is exceeded or undershot
- Flexible installation due to switchable orientation of display



| | |
|---|--|
| Art. no. | 32019 301 |
| Length measuring range | 12.7 mm |
| Digit increment | 0.01 mm |
| Min./max. measurement force | 0-2.5 N |
| Error limit | 0.02 mm |
| Data transmission type | DIGIMATIC |
| IP protection class | IP 66 |
| Functions | ABS function, On/Off, Hold-function (AE lock), Preset function, Reversal of counting direction |
| Absolute function | Yes |
| Automatic switch-off | No |
| Dynamic measurement | No |
| Preset function | Yes |
| Shank diameter | 8 mm |
| Tolerance value entry | Yes |
| Manual tolerance markers | No |
| Calibration Group | CE |
| Colour reading classification | No |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 1,5 V SR44 |
| Rotating housing | No |
| Combined indicator for figure/scale reading | No |
| Reversible counting direction | Yes |
| Digit height | 6.2 mm |
| Design | Metric |
| Display | Digital |
| Calibration Group Description | Dial gauge |
| WEEE (taking back waste electrical and electronic equipment) | 5 |

EAN-Code

4946368554181