

Deburring machine GIE



Application:

Steel, non-ferrous metal and stainless steel workpieces can be quickly and effectively deburred using the deburring machine GIE. Can be used as a bench-top device or optional with machine foot.

Version:

- low vibration and noise
- with emergency stop switch

Advantage:

- efficient deburring using wire brushes and commercial polishing tools
- optional two-stage speed adjustment
- integrated suction system in combination with machine foot ref. no. 390



Art. no.	78238 410
Model	GRIT GIE
Max. tool width	60 mm
Max. tool diameter	250 mm
Total motor speed	1500/3000 rpm
Motor output	1.5 kW
Weight	34 kg

EAN-Code

4014586859057