

Product information

71 72 460

Bolt Cutter



- Cutting capacity up to 48 HRC hardness
- Robust cutting edges are additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Forged-in stopper with comfortable shock-absorber
- Good access due to very flat construction of head and joint area
- Ergonomically angled handles to minimise effort
- Sturdy non-slip two-colour multi-component handle sleeves
- Precise adjustment (12 positions) by eccentric bolt
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Bolted cutter head, replaceable
- Joint: special tool steel, forged
- Handles: steel tube, powder-coated
- Blade: chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

Article No.	71 72 460
EAN	4003773066750
Head	grey atramentized
Handles	with multi-component grips
Weight	2,100 g
Dimensions	460 x 119 x 34 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

HRC 19	Ø 8 mm
HRC 40	Ø 6 mm
HRC 48	Ø 5 mm
Cutting edge length mm	30 mm
Head thickness	33 mm

technical change and errors excepted



