


DATASHEET

RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 0,25m



General data

The Cat.6A RJ45 patch cable **manufactured in Europe** guarantees very good characteristics for **10 Gigabit** Ethernet applications. The patch cable is composed of the Cat.7 raw cable **UC900 SS27 Cat.7 PUR** from Draka and **TM21** connectors from Hirose. Due to the **highly abrasion-resistant PUR** outer sheath, the cable is **resistant to mineral oil and ASTM oil**.

Cross section 4 x 2 x AWG27/7

Mounted anti-kink grommet

Temperature range **-35°C ~ +75°C**

Allgemeine Daten

Suitable for degree of protection (IP)	IP20
Cable type	S/FTP
Pin assignment	1:1
Contacts	Gold plated μ" gold plated
Locking lever	True
Connector type	TM21 red
Fire retardant version	True

This datasheet was created automatically on 27-02-2024 . Technical changes reserved.



DATASHEET

RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 0,25m

Model	Shielded
Length imprint	False
Anti-kink sleeve	put-on
Allocation	acc. TIA/EIA 568B
Jacket Material	Polyurethan (PUR)
Area of Application	Industrial Ethernet
Colour outer sheath	red
Category	6A (IEC)
Current Rating	max. 1 A
Cable type acc. to Manufacturer	Draka UC900 SS27 Cat.7 PUR
UV resistance	acc. IEC60068-2-5
Halogen free	True
Colour anti-kink sleeve	black

Mechanische Eigenschaften

Bending radius	25 mm
Conductive shield	360° shield contact
Mating cycles	≥ 750

Kabelaufbau

Raw cable	Cat.7
Type of connector connection 2	RJ45 8(8)
AWG-size	27/7
Type of connector connection 1	RJ45 8(8)
Conductor Material	Copper
Cable construction	4x2

Kabelmantel

Ozone resistance	acc. EN60811-2-1
Oil resistant (according to EN 60811-404)	False
Halogen-free	yes
Flame retardant	acc. IEC60332-1
Oil resistant	No
Euro class	Eca
Outer diameter of the cable	5.9 mm

This datasheet was created automatically on 27-02-2024 . Technical changes reserved.



DATASHEET

RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 0,25m

Low smoke	acc. IEC61034
-----------	---------------

Umgebungsbedingungen

Temperature Range (Installation)	-5 - 50 °C
Temperature Range (Operation)	-35 - 75 °C

Elektrische Eigenschaften

Conductor resistance DC	170 Ω/km
Resistance unbalance	< 3 %
Loop resistance	< 340 Ω/km
Test voltage	1000 V DC, 1min
Contact Resistance	< 20 mΩ
POE class	PoE+ acc. to IEEE802.3at
NVP value	79 %
Operating-/ tempering voltage	max. 50 V DC
Impedance	100 ±5 Ω
Insulation Resistance	≥ 2000 MΩ

Übertragungstechnische Eigenschaften

Transmission	5Gbit
Bandwidth	500MHz

Normen, Zulassungen, Zertifizierungen

Cabling standard	EN50173
Harmonised Standard	EN 50575
Oil resistant (acc. EN 60811-2-1)	True
Connector	IEC 60603-7-51

Available variants

ArtNr.	Bezeichnung	Length Längentoleranz	
K8048PUI0,25	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 0,25m	0.25 m	±5 %
K8048PUI0,5	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 0,5m	0.5 m	±5 %
K8048PUI1	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 1m	1.0 m	±5 %
K8048PUI1,5	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 1,5m	1.5 m	±5 %
K8048PUI2	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 2m	2.0 m	±5 %

This datasheet was created automatically on 27-02-2024 . Technical changes reserved.



DATASHEET

RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 0,25m

K8048PUI3	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 3m	3.0 m	±5 %
K8048PUI5	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 5m	5.0 m	±5 %
K8048PUI7,5	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 7,5m	7.5 m	±5 %
K8048PUI10	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 10m	10.0 m	±5 %
K8048PUI15	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 15m	15.0 m	±5 %
K8048PUI20	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 20m	20.0 m	±5 %
K8048PUI25	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 25m	25.0 m	±5 %
K8048PUI30	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 30m	30.0 m	±5 %
K8048PUI40	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 40m	40.0 m	±5 %
K8048PUI50	RJ45 Patch Cord Cat.6A S/FTP PUR Draka UC900 TM21 red 50m	50.0 m	±5 %

This datasheet was created automatically on 27-02-2024 . Technical changes reserved.

