

#### Shock-Safe Fuseholder, 5 x 20 / 6.3 x 32 mm, Slotted Cap / Fingergrip, Snap-in stepless





Shock-Safe Fuseholder Socket with Fingergrip Cap

Shock-Safe Fuseholder Socket with Slotted Cap

# 500 VAC · 4 W / 16 A (VDE) · 600 VAC/VDC · 32 A (UL/CSA)

#### See below:

#### **Approvals and Compliances**

#### **Description**

- Fuseholder for 600 VAC applications
- Fuseholder with high rated power acceptance
- Screw type fuse carrier

# **Unique Selling Proposition**

- Fuseholder for high performance applications
- High protection class IP67
- Easy, stepless snap-in mounting

- Equipment with three-phase supply (400 VAC)
- Applications with rated current up to 16 A (VDE)

#### Weblinks

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Accessories, Detailed request for product, Microsite

#### **Technical Data**

Shock-Safe Category	PC2
Fuse-Link	5 x 20 / 6.3 x 32 mm
Mounting	Panel mount, Front Side
Attachment	Snap-in
Terminal	Solder / Quick-Connect 6.3 x 0.8 mm
Rated Voltage	500 VAC (VDE), 600 VAC/VDC (UL/CSA)
Rated current	16A (VDE), 32A (UL/CSA)
Rated Power Acceptance IEC	4W / 16A @ Ta 23°C
	Admissible power acceptance at higher
	ambient temperature see derating cur-
	ves
Degree of Protection	IP67
Protection Class	Suitable for appliances with protection
	-land Land Land 150 044 40
	class I or II acc. to IEC 61140
Admissible Ambient Air Temp.	-40 °C to 85 °C
Admissible Ambient Air Temp. Climatic Category	
	-40°C to 85°C
Climatic Category	-40 °C to 85 °C 40/085/21 acc. to IEC 60068-1
Climatic Category Material: Socket	-40 °C to 85 °C 40/085/21 acc. to IEC 60068-1 Thermoplastic, black, UL 94V-0
Climatic Category Material: Socket Material: Terminals	-40 °C to 85 °C 40/085/21 acc. to IEC 60068-1 Thermoplastic, black, UL 94V-0 Tin-Plated Copper
Climatic Category Material: Socket Material: Terminals Unit Weight	-40 °C to 85 °C 40/085/21 acc. to IEC 60068-1 Thermoplastic, black, UL 94V-0 Tin-Plated Copper 36.1 g / 39.4 g
Climatic Category Material: Socket Material: Terminals Unit Weight Storage Conditions	-40 °C to 85 °C  40/085/21 acc. to IEC 60068-1  Thermoplastic, black, UL 94V-0  Tin-Plated Copper  36.1 g / 39.4 g  0 °C to 60 °C, max. 70% r.h.

Soldering Methods	Iron
	Soldering Profile
Solderability	350°C / 3 sec acc. to IEC 60068-2-20,
	Test Ta, method 2
Resistance to Soldering Heat	350°C / 10 sec acc. to IEC 60068-2-20
Solderability	350°C / 3 sec acc. to IEC 60068-2-20,
	Test Ta, method 2
Contact Resistance	≤ 10 mΩ at 100 mA acc. to IEC
	60127-6
Dielectric Strength	> 3 kV between life parts
	(50 Hz: 1 min)
Impulse Withstand Voltage	> 4 kV between life parts
Insulation Resistance	≥ 10 MΩ between life parts
	(500 VDC: 1 min)
Overvoltage Category	III acc. to IEC 60664-1
Pollution Degree	3 acc. to IEC 60664-1
Resistance to Vibration	acc. to IEC 60068-2-6, test Fc
Panel Thickness	1.0 - 3.0 mm

#### **Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

#### **Approvals**

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FUS

Approval Logo	Certificates	Certification Body	Description
VDE	VDE Approvals	VDE	VDE Certificate Number: 40044384
<b>, 511</b> <sub>118</sub>	UL Approvals	UL	UR File Number: E39328

#### **Product standards**

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u> .	Designed according to	IEC 60127-6	Miniature fuses. Part 6. Fuse-holders for miniature fuse-links
(UL)	Designed according to	UL 4248-1	Industrial Control Equipment
GF Group	Designed according to	CSA C22.2 no. 4248.1	Industrial Control Equipment

# **Application standards**

Application standards where the product can be used


Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements
<u>IEC</u>	Designed for applications acc.	IEC 60335-1	Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.

#### Compliances


The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
<b>50</b>	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
00	White Paper Glow wire test	SCHURTER AG	Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 &-13.

# Dimension [mm] 70.6 mm











Plate thickness 1mm

Plate thickness 1.5, 2.0, 3.0mm

# **Derating Curves**



Ambient Air Temperature Ta °C

# **All Variants**

Holder	Сар	Fuse-Link	Terminal	Degree of Pro- tection	Order Number
•	slotted	5 x 20mm	Quick-Connect 6.3 x 0.8 mm	IP67	0031.9156
•	slotted	6.3 x 32mm	Quick-Connect 6.3 x 0.8 mm	IP67	0031.9157
•	Fingergrip	5 x 20mm	Quick-Connect 6.3 x 0.8 mm	IP67	0031.9158
•	Fingergrip	6.3 x 32mm	Quick-Connect 6.3 x 0.8 mm	IP67	0031.9159
•	slotted	5 x 20mm	Solder	IP67	0031.9160
•	slotted	6.3 x 32mm	Solder	IP67	0031.9161
•	Fingergrip	5 x 20mm	Solder	IP67	0031.9162
•	Fingergrip	6.3 x 32mm	Solder	IP67	0031.9163

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging Unit Bulk (25 pcs.)

#### **Accessories**

#### Description

