



Safety Data Sheet 1907/2006/EC

Date printed 29.07.2020, Revision 29.07.2020

Version 05. Supersedes version: 04

Page 1 / 8

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Part code: 6283037 - LLG-Absorbent, 1,5kg oil and chemical binder, granules

1.2 Relevant identified uses of the substance or mixture and uses advised against

1.2.1 Relevant uses

Oil and chemical binder

1.2.2 Uses advised against

None known.

1.3 Details of the supplier of the safety data sheet

Company Lab Logistics Group GmbH
Am Hambuch 1
53340 Meckenheim
Germany
Tel.: +49(0)2225 92 11 0
Fax: +49(0)2225 92 11 11

**Address enquiries to
Safety Data Sheet**

info@llg-labware.com

1.4 Emergency telephone number

Advisory body +49 (0) 2225-92 11 48 (advisory service in German or English language)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture [REGULATION (EC) No 1272/2008]

No classification.

2.2 Label elements

The product does not require a hazard warning label in accordance with GHS/CLP-directives.

Hazard pictograms none

Signal word none

Hazard statements none

Precautionary statements none

2.3 Other hazards

Human health dangers May cause irritation of eyes, mucous membranes and respiratory organs.

Environmental hazards Does not contain any PBT or vPvB substances.

Other hazards Further hazards were not determined with the current level of knowledge.

SECTION 3: Composition / Information on ingredients

3.1 Substances

The product is a mixture.

3.2 Mixtures

Comment on component parts No dangerous components.
Substances of Very High Concern - SVHC: substances are not contained or are below 0.1%.

Postal address
Lab Logistics Group GmbH
Am Hambuch 1
D-53340 Meckenheim

Phone
+49 (0)22 25/92 11-0
Fax
+49 (0)22 25/92 11-11

Web
www.LLG.de
E-mail
info@LLG.de

General manager
Michael Simon
Tax identification number
DE 812727887

Commercial register
No. HRB 10800
Court of registration
Bonn



**SECTION 4: First aid measures****4.1 Description of first aid measures**

| | |
|----------------------------|---|
| General information | Change powdered clothing. |
| Inhalation | Ensure supply of fresh air. In the event of symptoms seek medical treatment. |
| Skin contact | In case of contact with skin wash off with warm water. Consult a doctor if skin irritation persists. |
| Eye contact | Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. |
| Ingestion | Rinse out mouth and give plenty of water to drink. Get medical advice. |

4.2 Most important symptoms and effects, both acute and delayed

No information available.

4.3 Indication of any immediate medical attention and special treatment neededTreat symptomatically.
Forward this sheet to the doctor.**SECTION 5: Fire-fighting measures****5.1 Extinguishing media**

| | |
|--|---|
| Suitable extinguishing media | foam, dry powder, water spray jet, carbon dioxide |
| Extinguishing media that must not be used | Full water jet. |

5.2 Special hazards arising from the substance or mixture

Risk of formation of toxic pyrolysis products.

5.3 Advice for firefightersUse self-contained breathing apparatus.
Fire residues and contaminated firefighting water must be disposed of in accordance within the local regulations.**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures**

Avoid dust formation.

6.2 Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

6.3 Methods and material for containment and cleaning upTake up mechanically. Avoid production of dust.
Dispose of absorbed material in accordance within the regulations.**6.4 Reference to other sections**

See SECTION 8+13

SECTION 7: Handling and storage**7.1 Precautions for safe handling**Avoid the formation and deposition of dust.
Binder is combustible.
Wash hands before breaks and after work.
Use barrier skin cream.
Do not eat, drink or smoke when using this product.

7.2 Conditions for safe storage, including any incompatibilities

Keep only in original container.
 Do not store together with food and animal food/diet.
 Store in a dry place.

7.3 Specific end use(s)

See product use, SECTION 1.2

SECTION 8: Exposure controls / personal protection

8.1 Control parameters

Ingredients with occupational exposure limits to be monitored (GB)

| |
|---|
| Substance |
| Silicium dioxide |
| CAS: 112926-00-8/7631-86-9, EINECS/ELINCS: 231-545-4 |
| Long-term exposure: 2.4 mg/m ³ , respirable dust; inhalable dust - 6 mg/m ³ |
| Sodium polyacrylate |
| CAS: 60323-79-7, EINECS/ELINCS: Polymer |
| Long-term exposure: 0,05 mg/m ³ , alveolar ducts super-absorbent polymer dust (diameter <10 microns) |

8.2 Exposure controls

Additional advice on system design Ensure adequate ventilation on workstation.
 Pay attention to dust limit value (ACGIH-2011: 10 mg/m³ particle inhalable; 3 mg/m³ particle respirable).

Eye protection Safety glasses. (EN 166:2001)

Hand protection The details concerned are recommendations. Please contact the glove supplier for further information.
 0,4 mm; Butyl rubber, >120 min (EN 374-1/-2/-3).

Skin protection Light protective clothing.

Other Avoid contact with eyes and skin.
 Do not inhale dust.

Respiratory protection Respiratory protection in the case of dust formation.
 Particle filter half mask, type FFP1 (DIN EN 149)

Thermal hazards not applicable

Delimitation and monitoring of the environmental exposition Comply with applicable environmental regulations limiting discharge to air, water and soil.

SECTION 9: Physical and chemical properties**9.1 Information on basic physical and chemical properties**

| | |
|--|-------------------|
| Form | powder > 10 µm |
| Color | light green |
| Odor | odourless |
| Odour threshold | not determined |
| pH-value | not applicable |
| pH-value [1%] | 6-7 |
| Boiling point [°C] | not applicable |
| Flash point [°C] | not determined |
| Flammability (solid, gas) [°C] | not determined |
| Lower explosion limit | not determined |
| Upper explosion limit | not determined |
| Oxidising properties | no |
| Vapour pressure/gas pressure [kPa] | not applicable |
| Density [g/ml] | not determined |
| Bulk density [kg/m³] | > 360 |
| Solubility in water | insoluble |
| Partition coefficient [n-octanol/water] | not determined |
| Viscosity | not applicable |
| Relative vapour density determined in air | not applicable |
| Evaporation speed | not applicable |
| Melting point [°C] | not determined |
| Autoignition temperature [°C] | > 440 (DIN 51794) |
| Decomposition temperature [°C] | 240 |

9.2 Other information

none

SECTION 10: Stability and reactivity**10.1 Reactivity**

No dangerous reactions known if used as directed.

10.2 Chemical stability

The product is stable under standard conditions.

10.3 Possibility of hazardous reactions

No hazardous reactions known.

10.4 Conditions to avoid

Strong heating, because the thermal decomposition starts from 240°C.

10.5 Incompatible materials

No information available.

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: Toxicological information**11.1 Information on toxicological effects****Acute toxicity**

Serious eye damage/irritation Based on the available information, the classification criteria are not fulfilled.

Skin corrosion/irritation Based on the available information, the classification criteria are not fulfilled.

Respiratory or skin sensitisation Based on the available information, the classification criteria are not fulfilled.

Specific target organ toxicity — single exposure Based on the available information, the classification criteria are not fulfilled.

Specific target organ toxicity — repeated exposure Based on the available information, the classification criteria are not fulfilled.

Mutagenicity Based on the available information, the classification criteria are not fulfilled.

Reproduction toxicity Based on the available information, the classification criteria are not fulfilled.

Carcinogenicity Based on the available information, the classification criteria are not fulfilled.

General remarks

Toxicological data of complete product are not available.
The toxicity data listed pertaining to the ingredients are intended for those working in the medicinal professions, experts for occupational health and safety and toxicologists. The toxicity data pertaining to the ingredients were supplied by the manufacturers of raw materials.

SECTION 12: Ecological information**12.1 Toxicity****12.2 Persistence and degradability**

Behaviour in environment compartments No information available.

Behaviour in sewage plant No information available.

Biological degradability No information available.

12.3 Bioaccumulative potential

No information available.

12.4 Mobility in soil

No information available.

12.5 Results of PBT and vPvB assessment

Based on all available information not to be classified as PBT or vPvB respectively.

12.6 Other adverse effects

Do not discharge product unmonitored into the environment or into the drainage.
The toxicity data pertaining to the ingredients were supplied by the manufacturers of raw materials.

**SECTION 13: Disposal considerations****13.1 Waste treatment methods**

Waste material must be disposed of in accordance with the Directive on waste 2008/98/EC as well as other national and local regulations. It is not possible to determine a waste code for this product in accordance with the European Waste Catalogue (EWC) since it is only possible to classify it according to how it is used by the customer. The waste code is to be determined within the EU in liaison with the waste-disposal operator.

Product

Coordinate disposal with the disposal contractor/authorities if necessary.
For recycling, consult manufacturer.

Waste no. (recommended) 150203

Contaminated packaging

Uncontaminated packaging may be taken for recycling.

Waste no. (recommended) 150101

SECTION 14: Transport information**14.1 UN number**

Transport by land according to ADR/RID not applicable

Inland navigation (ADN) not applicable

Marine transport in accordance with IMDG not applicable

Air transport in accordance with IATA not applicable

14.2 UN proper shipping name

Transport by land according to ADR/RID NO DANGEROUS GOODS

Inland navigation (ADN) NO DANGEROUS GOODS

Marine transport in accordance with IMDG NOT CLASSIFIED AS "DANGEROUS GOODS"

Air transport in accordance with IATA NOT CLASSIFIED AS "DANGEROUS GOODS"

14.3 Transport hazard class(es)

Transport by land according to ADR/RID not applicable

Inland navigation (ADN) not applicable

Marine transport in accordance with IMDG not applicable

Air transport in accordance with IATA not applicable





14.4 Packing group

Transport by land according to ADR/RID not applicable

Inland navigation (ADN) not applicable

Marine transport in accordance with IMDG not applicable

Air transport in accordance with IATA not applicable

14.5 Environmental hazards

Transport by land according to ADR/RID no

Inland navigation (ADN) no

Marine transport in accordance with IMDG no

Air transport in accordance with IATA no

14.6 Special precautions for user

Relevant information under SECTION 6 to 8.

14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EEC-REGULATIONS 2008/98/EC 2000/532/EC; 2010/75/EU; 2004/42/EC; (EC) 648/2004; (EC) 1907/2006 (REACH); (EU) 1272/2008; 75/324/EEC ((EC) 2016/2037); (EU) 2015/830; (EU) 2016/131; (EU) 517/2014

TRANSPORT-REGULATIONS ADR (2019); IMDG-Code (2019, 39. Amdt.); IATA-DGR (2020)

NATIONAL REGULATIONS (GB): EH40/2005 Workplace exposure limits (Second edition, published December 2011).

- Observe employment restrictions for people no

- VOC (2010/75/CE) not applicable

15.2 Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information**16.1 Abbreviations and acronyms:**

ADR = Accord européen relatif au transport international des marchandises Dangereuses par Route
RID = Règlement concernant le transport international ferroviaire de marchandises dangereuses
ADN = Accord européen relatif au transport international des marchandises dangereuses par voie de navigation intérieure
ATE = acute toxicity estimate
CAS = Chemical Abstracts Service
CLP = Classification, Labelling and Packaging
DMEL = Derived Minimum Effect Level
DNEL = Derived No Effect Level
EC50 = Median effective concentration
ECB = European Chemicals Bureau
EEC = European Economic Community
EINECS = European Inventory of Existing Commercial Chemical Substances
EL50 = Median effective loading
ELINCS = European List of Notified Chemical Substances
EmS = Emergency Schedules
GHS = Globally Harmonized System of Classification and Labelling of Chemicals
IATA = International Air Transport Association
IBC-Code = International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk
IC50 = Inhibition concentration, 50%
IMDG = International Maritime Code for Dangerous Goods
IUCLID = International Uniform Chemical Information Database
LC50 = Lethal concentration, 50%
LD50 = Median lethal dose
LC0 = lethal concentration, 0%
LOAEL = lowest-observed-adverse-effect level
LL50 = Median lethal loading
LQ = Limited Quantities
MARPOL = International Convention for the Prevention of Marine Pollution from Ships
NOAEL = No Observed Adverse Effect Level
NOEC = No Observed Effect Concentration
PBT = Persistent, Bioaccumulative and Toxic substance
PNEC = Predicted No-Effect Concentration
REACH = Registration, Evaluation, Authorisation and Restriction of Chemicals
STP = Sewage Treatment Plant
TLV@TWA = Threshold limit value – time-weighted average
TLV@STEL = Threshold limit value – short-time exposure limit
VOC = Volatile Organic Compounds
vPvB = very Persistent and very Bioaccumulative