



Part no.: 50114617
TKS 30x45
Reflector

Figure can vary

Contents

- Technical data
- Dimensioned drawings

Part no.: 50114617 – TKS 30x45 – Reflector

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	31.5 mm
Reflection surface width	29 mm
Mounting dimension, height	55.5 mm
Reflection surface height	44 mm
Mounting dimension, thickness	8 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	20 g
Type of fastening	Adhesive Through-hole mounting

Environmental data	
Ambient temperature, operation	-40 ... 65 °C

Certifications	
Degree of protection	IP 67

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

