

Screw tap, HSSE Ultra HL oversize 7GX M 7GX 0° 371 B

for universal use up to 1000 N/mm²

ATORN®



Application

For producing metric threads on CNC machines or conventional machines in **through holes** in steel, stainless steel, non-ferrous metals, cast iron and special alloys up to 1200 N/mm².

Advantage

- Ideal for long service life requirements and materials that are difficult to machine, such as stainless steel
- Innovative cutting geometry and ULTRA HL coating guarantee high process reliability even under difficult machining conditions

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	18	12	8	11	10	19	19	17	19	17	18	13		18	7	6	6		

Art. No.	13041 600
Type	UNI MAX 45HL Control
Thread type	Metric thread
Thread type x nominal diameter	M30
Pitch	3.5 mm
Hole type	Clearance hole ≤ 3xD
Cutting material	HSSE
Surface	ULTRA HL
Lead angle shape	B
Tolerance of screw taps	7GX
Twist angle	0°
Shaft diameter	22 mm
Application type/machine type	CNC, Conventional
Core hole diameter	26.5 mm
Coolant supply	External
Length	180 mm
Shank square	18 mm
Cutting speed (steel 1000) suitability	1
Cutting speed (steel 1300) suitability	2
Overall stainless steel suitability	1
fitness not iron total	1
fitness Titan/Nickel/Super total	1
Cutting speed (cast) suitability	1
Cutting speed (hard 55) suitability	3
Cutting speed (hard 65) suitability	3
DIN	376

EAN-Code

4050293649321