

Angle standard 90°, triangular form

Highest accuracy



Application:

For simple and precise checking of the 90° angle. Ideal for use on hard stone bases, e.g. for checking straightness in vertical height measuring devices; also suitable as a contact surface for large components. Also suitable for checking the 90° angle e.g. in coordinate measuring instruments and machine tools.

Execution:

- Carefully selected and flawless South African hard stone material – Diabas.
- with through-bore(s) for weight reduction
- Exactly 2-sided. The two precisely shaped surfaces are finely machined to a high-quality finish to be flat and at exact angles to one another. The remaining surfaces are finely machined
- LAB accuracy: surface finely ground and lapped to maximum fineness
- can be used horizontally and vertically
- Calibration certificate included in the scope of delivery. measurement results are based on national standards
- DAkkS calibration certificate available on request

Delivery:

Calibration certificate. Measurement results are based on national standards from the German National Metrology Institute in Brunswick, Germany.



| | |
|------------------------------|------------------|
| Art. no. | 35283 081 |
| Brand | JFA |
| Limb length | 800 mm |
| Limb length 2 | 500 mm |
| Width | 80 mm |
| Number of drill holes | 1 PCS |
| Weight | 55 kg |
| JFA precision LAB | 0.002 mm |
| Gross Weight | 74.000 kg |
| Product Group | 341 |