

Drawer cabinet system 550 S with 9 drawers

Depth 550 mm, width 722 mm

Execution:

- Solidly welded steel sheet construction
- Tilt-proof due to built-in individual drawer pull-out locking
- The drawers have high-quality Delrin rollers which means that they run quietly
- Drawers with slots all around for inserting compartment rails and dividers
- Perforated steel sheet base (25 mm hole spacing) for fastening and fixing components
- Aluminium grip handles with paper and cellophane strips and lateral cover caps
- For drawer front height 60 mm, the load capacity is 70 kg with evenly distributed load

Advantage:

- Optimum operating characteristics of drawers
- High quality - made in Germany

Art. no.	50295 052
Brand	HK
Manufacturer Part Number	50295052
Number of drawers	9 PCS
With doors	No
Height	1036 mm
Width	722 mm
Depth	550 mm
Height x width x depth	1036 x 722 x 550 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	600 x 450 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	100 kg
Drawer surface	0.27 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	No
With single pull-out safety brake	Yes
Central locking	Yes
Material of cover panel	Wood, plastic-coated
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Functions	RFID possible
Model	S5 32/9
Overall surface	2.43 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	145.000 kg
Product Group	5BB

FH mm	KH mm
60	40
60	40
60	40
90	70
90	70
120	100
150	130
150	130
180	130



EAN

4039247461950