

electric chain hoist Pro/DC-Pro, 2-stage

load capacity: 125-2000 kg

DEMAG

Application:

The electric chain hoist Pro is characterised by a low installation cost and high operating comfort, and is suitable for all applications with high loads such as shift operations.

Execution:

- Plug and lift—all chain block electric connections are plug-in
- With a hinged, universal suspension bracket, the tension can simply be suspended in the wheel set
- The length of the control cable can be adjusted without any additional wiring effort
- Fatigue-free operation due to ergonomically optimised and robust control switch DSC
- Fast change of the entire chain drive without dismantling the motor or transmission parts
- Contactor protection 24 V, degree of protection IP55
- Operating hour meter
- Operation limit switch for top-most/bottom-most hook position

Advantage:

- Service room
- Infrared diagnostic interface
- Speed-monitored brake/sliding clutch operating principle
- Minimum 1900 full-load hours



Art. no.	77099 763
Brand	DEMAG
Manufacturer Part Number	93003046
Load-carrying capacity	125 kg
Lift height	5 m
Stroke speed control	In two steps
Stroke speed of precision hoist	2 m/min
Stroke speed of main hoist	8 m/min
Number of load chains	1 PCS
Construction height	364 mm
Length	422 mm
Depth	268 mm
Model	DC-Pro 1-125 V8/2
FEM group	4 m
Colour	Azure blue RAL 5009
Gross Weight	22.000 kg
Product Group	774