

Manual vacuum lifter with 2 aluminium suction heads

Handle mounted crossways, carrying capacity 70 kg

Application:

For the safe and secure lifting, carrying and holding of discs, sheets and panels.

Execution:

- Lever-type vacuum lifter
- 2 aluminium suction heads
- Handle mounted crossways to the suction heads

Advantage:

- Ergonomic handle
- Robust aluminium body



Art. no.	77178 025
Brand	BOHLE
Manufacturer Part Number	BO 602 OBL
Load-carrying capacity	70 kg
Direction of force	Parallel
Material	Aluminium
Number of suction heads	2 PCS
Suction head diameter	120 mm
Number of pieces in assortment/set	1 PCS
Gross Weight	1.056 kg
Product Group	7EM

EAN

4010122602019