

# **Temperature Accessories**

## **Contact Probes**

## 80PK-22 SureGrip™ Immersion Probe

- Type-K thermocouple for use in liquids and gels
- Measurement range: -40 to 1090°C



### 80PK-1 and 80PJ-1 Bead Probe

- 80PK-1: Type-K thermocouple for general purpose applications
- 80PJ-1 operates with Jtype thermometers
- Measurement range: -40 to 260°C



## **DMM Probes**

## 80AK Thermocouple Adapter

- Adapts Type-K thermocouple mini-connector to dual banana plug inputs
- Measurement range and accuracy: probe dependent
- Suitable for low voltage applications (below 30 V AC, 60 V DC)

## 80PK-24 SureGrip™ Air Probe

- Type-K thermocouple for use in air and non-caustic gas measurements
- · Bead protected by perforated baffle
- Measurement range: -40 to 816°C

### 80PK-3A Surface Probe

- Type-K thermocouple for flat or curved surfaces such as plates and rollers
- Measurement range: 0 to 260°C



## **80BK Integrated DMM Probe**

- Type-K thermocouple with standard banana jack
- Convenient one piece construction
- Compatible with DMMs with temperature measurement functions
- Measurement range: -40 to 260°C

80TK Thermocouple Module • Converts a DMM to a thermometer

## 80PK-25 and 80PT-25 SureGrip™ **Piercing Probe**

- 80PK-25: Type-K thermocouple suitable for food industry, liquids and gels
- 80PT-25 operates with T-type thermometers
- Measurement range: 80PK-25: -40 to 350°C 80PT-25: -196 to 350°C

## 80PK-8 Pipe Clamp Temperature Probe

- fast temperature and of pipe surfaces
- Durable ribbon sensor
- Measurement range: -29 to 149°C for pipe diameters from 6.4 to 34.9mm

## voltage applications (below 24 V AC, 60 V DC)



 Measurement range: -50 to 1000°C (probe dependent)

• For use with type-K

thermocouples in low



# 80PK-26 SureGrip™ General Purpose

- Type-K thermocouple with tapered tip for use in air, non-caustic gas and surface applications
- Measurement range: -40 to 816°C

# • Type-K thermocouple for

- superheat measurements

## 80T-150U Universal Temperature Probe

- Compatible with Fluke DMM
- · High accuracy, fast reading for low voltage (below 24 V AC, 60 V DC) applications
- Measurement range: -50 to 150°C
- Output: 1 mV/°C or 1 mV/°F (switchable)



# **Probe**


## 80PK-9 and 80PJ-9 General **Purpose Probe**

- 80PK-9: Type-K thermocouple surface, air and non-caustic gases
- 80PJ-9 operates with J-type thermometers
- Measurement range: -40°C to 260°C



## 80PK-27 SureGrip™ Industrial Surface Probe

- Type-K thermocouple for surfaces in rugged environment
- · Durable ribbon sensor
- Measurement range: 127 to 600°C



applications • Total length of cable: 1m (0.5m in cable, 0.5m in Velcro cuff insulation material; Hytrel)

• Measurement range: -30°C to 105°C



SureGrip™ accessories are designed to improve steadiness in slippery hands. Rubber overmolded surfaces and finger-hugging curves give the user a comfortable, reliable grip on the accessory so they can focus on making an accurate measurement.





# **Temperature Accessories**

## Other Temperature Accessories


### 80PR-60 RTD Temperature Probe

· For simulaneously taking contact and noncontact temperature measurements with Fluke 66 or 68

 Measurement range: -40 to 260°C

### 80CK-M & 80CJ-M type K & J Male **Mini-Connectors**

· Isothermal screw terminal for K or J wire




· Color coded to industry standards (K-yellow, J-black)

• Two per package







Thermocouple Plug Kits

Type C (red), one Type N (orange), one

#### 700TC2

A kit of 7 mini-plug connectors Type J (black), two Type K (yellow), two

Type E (purple), one Type T (blue), one Type R/S (green), one



## 80PK-EXT, 80PJ-EXT and **80PT-EXT Extension Wire Kits**

• Extending and repairing J, K ot T-type thermocouple wires

• Kit includes 3 meters of thermocouple wire and 1 pair of male/female mini-connectors

• Maximum continuous exposure temperature: 260°C

• 80PK-EXT is compatible with K-type thermometers, 80PJ-EXT is designed for J-type thermometers and PT-EXT for T-type thermometers



## **Temperature Probe Compatibility Chart**

	114/115/116/117	175/177	179	187/189	27	8845A/8846A	ZZIV	83V	87V	88V	43B	120 Series	190 Series	1577	1587	51/52/53/54 II	561	89/99	705/707	714	715	724	725	741B/743B/744	787	789
Contact Probes																										
80PK-1 80PK-27	1	1	2	2	1	1	_1	1	2	2	1	1	1	1	2	•	•		1	•	1	•	•	•	1	_1_
80PJ-1, 80PJ-9																•				•	$\vdash$	•	•	•	$\vdash$	
80PT-25	٠.	-	-					_								•	_			•	$\vdash$	•	•	•	$\vdash$	
80PK-11	1																•									
DMM probes	- 21																									
80AK	●3) ●3)		•	•					•	•					•						$\vdash$	$\vdash$	<del></del>	$\vdash$	$\vdash$	_
80BK 80TK	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•				•		•	$\vdash$	$\vdash$	•	•	•
80T-150U		•	•	•	•						•	•	•									$\vdash$	$\vdash$			•
Miscellaneous																										_
80CK-M	1					1	1									•	•			•		•	•	•		_
80CJ-M	1					1	1									•	_			•		•	•	•	-	_
80PK-EXT	1	<del>                                     </del>		_		1	1									•				•	$\vdash$	•	•	•	-	_
80PJ-EXT	+ *					-	-									•				•		•	•	•	-	_
80PT-EXT																				•		•	•	•	-	_
700TC1, 700TC2																				•		•	•	•		_
80PR-60																		•								

- 1) Requires 80TK 2) Requires 80AK
- 3) Fluke 16 only