


DTI411



RFID read/write head HF

DTRHF FNRWIOUS03



Application

Application	detection of objects on transport equipment		
Radio approval for	Europe; USA; Canada; Japan; Australia; China; Taiwan; India; Singapore		

Electrical data

Operating voltage [V]	19.2...28.8 DC		
Current consumption [mA]	< 50		
Protection class	III		
Operating frequency [MHz]	13.56		
RFID standard	ISO 15693		

Detection zone

Distance write/read head front [mm]	90		
Distance write/read head side [mm]	25		
Distance to the ID tag [mm]	referred to 20 mm coin tag; I-CODE SLI	:	≤ 18

Interfaces

Communication interface	IO-Link		
Transmission type	COM2 (38.4 kBaud)		
IO-Link revision	1.1		
SDCI standard	IEC 61131-9		
IO-Link device ID	967 d / 00 03 C7 h		
Profiles	Smart Sensor: Device Identification		
SIO mode	no		
Required master port type	A		

Operating conditions

Ambient temperature [°C]	-20...60		
Storage temperature [°C]	-25...80		
Protection	IP 67; IP 69K		

DTI411

RFID read/write head HF

DTRHF FNRWIOUS03



Tests / approvals		
EMC		DIN EN 301489-3
Shock resistance		EN 60068-2-27
Vibration resistance		EN 60068-2-27
Radio approval		EN 300 330 V2.1.1
MTTF	[years]	613.74
	Ta	-20...60 °C
UL approval	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E205959
Mechanical data		
Weight	[g]	111.5
Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	M12 x 1 / L = 70
Thread designation		M12 x 1
Materials		housing: stainless steel; Protective cover: PPS
Displays / operating elements		
Display	operation	1 x LED, green
	tag communication	1 x LED, yellow
Remarks		
Remarks		only for static applications
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12		



DTI411



RFID read/write head HF

DTRHF FNRWIOUS03

Connection

