

OT80F3



OT80F3 SWITCH-DISCONNECTOR

General Information

| | |
|-----------------------|---|
| Extended Product Type | OT80F3 |
| Product ID | 1SCA105798R1001 |
| EAN | 6417019397016 |
| Catalog Description | OT80F3 SWITCH-DISCONNECTOR |
| Long Description | 3-pole, front operated, base mounted, DIN-rail mountable switch-diconnector / non-fusible disconnect switch with protected clamp terminals, handle and shaft are not included |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 10 piece |
| Customs Tariff Number | 85365080 |

Popular Downloads

| | |
|-----------------------------------|--|
| Data Sheet, Technical Information | 1SCC301020C0201 |
| Instructions and Manuals | 1SCC301064M0212 |
| Mechanical Drawings | 1SCC301450F0001 1SCC301449F0001 OT63-80F3.stp OT63-80F3.igs |

Dimensions

| | |
|----------------------------|---------|
| Product Net Width | 52.5 mm |
| Product Net Height | 91.5 mm |
| Product Net Depth / Length | 72.5 mm |
| Product Net Weight | 0.25 kg |

Technical

| | |
|--|--|
| Rated Operational Current AC-21A (I_e) | (380 ... 415 V) 80 A (500 V) 80 A (690 V) 80 A |
| Rated Operational Current AC-22A (I_e) | (380 ... 415 V) 80 A (500 V) 80 A (690 V) 80 A |
| Rated Operational Current AC-23A (I_e) | (380 ... 415 V) 75 A (500 V) 58 A (690 V) 20 A |

| | |
|--|--|
| Rated Operational Power AC-23A (P_e) | (220 ... 240 V) 22 kW (400 ... 415 V) 37 kW (500 V) 37 kW (690 V) 18.5 kW |
| Conventional Free-air Thermal Current (I_{th}) | q = 40 °C 80 A |
| Conventional Thermal Current (I_{the}) | Fully Enclosed 80 A |
| Rated Impulse Withstand Voltage (U_{imp}) | 8 kV |
| Rated Insulation Voltage (U_i) | acc. to IEC/EN 60664-1 750 V |
| Rated Operational Voltage | Main Circuit 750 V |
| Rated Short-Circuit Making Capacity (I_{cm}) | (690 V) 2.1 kA |
| Rated Short-time Withstand Current (I_{cw}) | for 1 s 1.5 kA |
| Power Loss | at Rated Operating Conditions per Pole 4.5 W |
| Pollution Degree | 3 |
| Handle Type | Knob Handle and shaft not included |
| Switches Operating Mechanism | Mechanism on Top of the Switch |
| Distance Between Phases | Standard |
| Position of Line Terminals | Top In - Bottom Out Bottom In - Top Out |
| Operating Mode | Front operated |
| Standards | IEC 60947-3 / UL 508 / CSA C22.2 No. 14 |
| Special Functions | No |
| Mounting Type | Base mounting |
| Number of Poles | 3 |
| Cable Cross-Section | 1.5...35 mm ² |
| Terminal Type | Screw Terminals |
| Tightening Torque | acc. IEC 60947-1 2 N·m |

Technical UL/CSA

| | |
|----------------------------------|---|
| Maximum Operating Voltage UL/CSA | 600 V |
| Horsepower Rating UL/CSA | (110 ... 120 V AC) Single Phase 2 Hp (240 V AC) Single Phase 10 Hp (440 ... 480 V AC) Single Phase 20 Hp (550 ... 600 V AC) Single Phase 20 Hp (220 ... 240 V AC) Three Phase 20 Hp (440 ... 480 V AC) Three Phase 40 Hp (550 ... 600 V AC) Three Phase 40 Hp |
| Ampere Rating UL/CSA | 80 A |
| Tightening Torque UL/CSA | 18 in·lb |

Environmental

| | |
|---------------------------|-----------------------------------|
| RoHS Status | Following EU Directive 2011/65/EU |
| Environmental Information | 1SCC301183D0201 |

Certificates and Declarations (Document Number)

| | |
|--------------------------------|-----------------|
| Declaration of Conformity - CE | 1SCC301167D2704 |
| Environmental Information | 1SCC301183D0201 |
| Instructions and Manuals | 1SCC301064M0212 |
| RoHS Information | 1SCC301183D0202 |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | 1 piece |
| Package Level 1 Width | 84 mm |
| Package Level 1 Depth / Length | 103 mm |
| Package Level 1 Height | 64 mm |
| Package Level 1 Gross Weight | 0.27 kg |
| Package Level 1 EAN | 6417019397016 |

Classifications

| | |
|----------------------------|--|
| E-nummer | 3170941 |
| Object Classification Code | Q |
| ETIM 5 | EC000216 - Switch disconnecter |
| ETIM 6 | EC000216 - Switch disconnecter |
| ETIM 7 | EC000216 - Switch disconnecter |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

