MOSFET - Power, Single N-Channel, D²PAK7 60 V, 2.5 mΩ, 169 A

NTBGS2D5N06C

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- Lowers Switching Noise/EMI
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage		V _{DSS}	60	V	
Gate-to-Source Voltage	Э		V _{GS}	±20	V
Continuous Drain Current R _{θJC} (Note 2)	Steady	T _C = 25°C	I _D	169	Α
Power Dissipation $R_{\theta JC}$ (Note 2)	State	1C = 25 C	P_{D}	136	W
$\begin{array}{c} \text{Continuous Drain} \\ \text{Current R}_{\theta JA} \\ \text{(Notes 1, 2)} \end{array}$	Steady State	, I. = 25°C		27	Α
Power Dissipation R _{θJA} (Notes 1, 2)	Oldio		P_{D}	3.7	V
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 100 \ \mu s$		I _{DM}	680	Α
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)			I _S	113	Α
Single Pulse Drain-to-Source Avalanche Energy (I _L = 23.1 A _{pk} , L = 1 mH)		E _{AS}	266	mJ	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		TL	260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


- 1. Surface-mounted on FR4 board using a 1 in², 1 oz. Cu pad.
- 2. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.



ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
60 V	2.5 m Ω @ 12 V	169 A
00 V	2.65 m Ω @ 10 V	109 A



- 1. Gate
- 2. Source
- 3. Source
- 4. Drain
- 5. Source 6. Source
- 7. Source

N-CHANNEL MOSFET



D²PAK7 CASE 221BP

MARKING DIAGRAM

BGS2D5 N06C **AYWWG**

BGS2D5N06C = Specific Device Code

= Assembly Location

= Year

WW = Work Week = Pb-Free Package

ORDERING INFORMATION

Device	Package	Shipping [†]
NTBGS2D5N06C	D ² PAK7 (Pb-Free)	800 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 2)	$R_{ hetaJC}$	1.1	°C/W
Junction-to-Ambient - Steady State (Note 1)	$R_{ hetaJA}$	40	


ELECTRICAL CHARACTERISTICS (T₁ = 25°C unless otherwise specified)

Parameter	Symbol	Test Cond	ition	Min	Тур	Max	Unit
OFF CHARACTERISTICS							•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /	I _D = 175 μA, ref to 25°C			18.4		mV/°C
Zero Gate Voltage Drain Current	ro Gate Voltage Drain Current I_{DSS} $V_{GS} = 0 \text{ V}$, $T_{J} = 25^{\circ}\text{C}$		T _J = 25°C			10	μΑ
		$V_{DS} = 60 \text{ V}$	T _J = 125°C			100	μΑ
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, V _{GS}	_S = 20 V			100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D$	= 175 μΑ	2.0	3.0	4.0	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J	I _D = 175 μA, re	f to 25°C		-8		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 12 V, I _E	₀ = 35 A		2.0	2.5	
		V _{GS} = 10 V, I _D = 17 A			2.2	2.65	mΩ
Gate-Resistance	R _G	T _A = 25°C			1.1		Ω
CHARGES, CAPACITANCES & GATE RESIS	TANCE						
Input Capacitance	C _{ISS}				3510		
Output Capacitance	C _{OSS}	V _{GS} = 0 V, V _{DS} = 30 V, f = 1 MHz			1950		pF
Reverse Transfer Capacitance	C _{RSS}				35		
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = 10 \text{ V}, V_{DS} = 30 \text{ V}; I_{D} = 35 \text{ A}$ $V_{GS} = 0 \text{ V}, V_{DS} = 50 \text{ V}$			45.4		
Threshold Gate Charge	Q _{G(TH)}				9		nC
Gate-to-Source Charge	Q _{GS}				14.7		
Gate-to-Drain Charge	Q _{GD}				6.8		
Output Charge	Q _{OSS}				90		
SWITCHING CHARACTERISTICS (Note 4)					•		
Turn-On Delay Time	t _{d(ON)}				17.9		
Rise Time	t _r	Vos = 10 V. Vo	c = 30 V.		9.3		1
Turn-Off Delay Time	t _{d(OFF)}	V_{GS} = 10 V, V_{DS} = 30 V, I_{D} = 35 A, R_{G} = 6 Ω			26.9		ns ns
Fall Time	t _f				13.6		
DRAIN-SOURCE DIODE CHARACTERISTIC	s						•
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V, I _S = 35 A	T _J = 25°C		0.82	1.2	
			T _J = 125°C		0.7		٧
Reverse Recovery Time	t _{RR}	$V_{GS} = 0 \text{ V, } dI_S/dt = 100 \text{ A/}\mu\text{s,}$ $I_S = 17 \text{ A}$			66		ns
Reverse Recovery Charge	Q _{RR}				77.5		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: pulse width \leq 300 μ s, duty cycle \leq 2%.

^{4.} Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Impedance


PACKAGE DIMENSIONS


D2PAK7 (TO-263-7LD) 15.4x9.9x4.5 CASE 221BP



- A. PACKAGE CONFORMS TO JEDEC TO-263 VARIATION CB EXCEPT WHERE NOTED. B. ALL DIMENSIONS ARE IN MILLIMETERS.
- D. DIMENSION AND TOLERANCE AS PER ASME Y14.5-2009.
 E. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
 F. LAND PATTERN RECOMMENDATION PER IPC.
- TO127P1524X465-8N.

DIM	MILLIMETERS			
DIM	MIN	NOM	MAX	
Α	4.30	4.50	4.70	
A1	0.00	0.10	0.20	
b2	0.60	0.70	0.80	
b	0.50	0.60	0.70	
С	0.40	0.50	0.60	
c2	1.20	1.30	1.40	
D	9.00	9.20	9.40	
D1	7.30	7.80	8.20	
Е	9.70	9.90	10.20	
E1	7.15	8.05	8.55	
е	~	1.27	~	
Н	15.10	15.40	15.70	
L	2.44	2.64	2.84	
L1	1.00	1.20	1.40	
L3	~	0.25	~	
aaa	~	~	0.25	





ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, Buyer shall indemni

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT
North American Technical Support:
Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative