

**Clamping yoke
KLBUE 4-13.5 SC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

**Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Type	KLBUE 4-13.5 SC
Order No.	1712311001
Version	Clamping yoke, Clamping yoke, Steel
GTIN (EAN)	4032248032358
Qty.	10 pc(s).

Data sheet

Clamping yoke KLBUE 4-13.5 SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	20.1 mm	Width (inches)	0.791 inch
Height	22 mm	Height (inches)	0.866 inch
Depth	31.45 mm	Depth (inches)	1.238 inch
Mounting dimension - width	18.9 mm	Net weight	17.3 g

Material data

Material	Steel	Colour	Silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on	Type of mounting	Screw

Conductors for clamping (rated connection)

Cable diameter, max.	13.5 mm	Cable diameter, min.	4 mm
----------------------	---------	----------------------	------

Dimensions

Length of thread	5.3 mm	Pitch in mm (P)	20 mm
------------------	--------	-----------------	-------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC002020
UNSPSC	30-21-18-01	eClass 6.2	27-14-11-90
eClass 7.1	27-14-11-50	eClass 8.1	27-14-11-50
eClass 9.0	27-14-11-50	eClass 9.1	27-14-11-50

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN_WSCAD
User Documentation	Beipackzettel_KLBUE.pdf