True Delay Off Timer (Delay On Release)



Terminal Protection to IP20


Dims: to DIN 43880 W. 17.5mm



- *NEW* 17.5mm DIN rail housing
- □ True Delay Off timing function
 - Adjustment of time delay range
- Dual-voltage input
- 1 x SPDT relay output 8A
- Green LED indication for supply status



FUNCTION DIAGRAM



INSTALLATION AND SETTING



Installation work must be carried out by qualified personnel.

- BEFORE INSTALLATION, ISOLATE THE SUPPLY.
- Connect the unit as shown in the diagram below.
- If 24V AC/DC operation is required then terminals "A1" and "A3" must be linked.

Setting the unit

Set the "Delay (t)" adjustment 2 as required.

Applying power

- Apply power and the green LED 1 will illuminate.
- The relay will energise and contacts 15 and 18 close.
- When the power is removed, the green LED will extinguish. The relay will remain energised for delay period "t" then de-energise. Contacts 15 and 18 will open.

Note:

The supply must be maintained for a minimum period of 500mS (t_s) for correct operation. For the 10 minute version, the minimum period is 1 second.

TECHNICAL SPECIFICATION 24V AC/DC¹ // 110V AC 24V AC/DC¹ // 230V AC Supply voltage Un (A1, A2, A31) terminals A1 and A3 are linked Frequency range: 48 - 63Hz Supply variation: Power consumption (@ 1.15 x Un) 24V 110V 230V 1.3VA 2.7VA 12.8VA 0.62W True Delay Off Timing function: Timing delay (t) options: Seconds: Minutes: 0.5 - 100.5 - 101 - 302 – 60 Min. power on period (t_s) 500mS 1 second (10 minute units) ± 1% at constant conditions Repeat accuracy: Power on indication: Green LED -20 to +60°C Ambient temp: Relative humidity +95% max. Output (15, 16, 18) SPDT relay 250V 8A (2000VA) Output rating: AC1 250V 3A 25V 8A (200W) DC1 Electrical life: ≥ 100,000 ops at rated load (AC1) Housing Orange flame retardant UL94 V0 Weight: ≈ 75g Mounting option: On to 35mm symmetric DIN rail to BS EN 60715 or direct surface mounting via 2 x M3.5 or 4BA screws using the black clips provided on the rear of the unit. Terminal conductor size ≤ 2 x 2.5mm² solid or stranded Approvals: CE, C-tick Cand RoHS Compliant.

CUL) US LISTED IND. CONT. EQ.

Note:

Supply voltage and time delay should be specified at the time of ordering.

