

Metal circular saw blade, HSS, coarse-toothed with taper tap and third tap, type C

for universal use up to 1000 N/mm² in larger cross sections and cutting depths on conventional machines

ORION[®]

Application:


For creating separation cuts in medium to large cutting depths in the material groups of steel, (stainless steel), cast iron and (non-ferrous metals) up to a strength of 1000 N/mm².

Execution:

- precision-ground metal circular saw blade with tooth type B, coarse serrated with taper tap and third tap, laterally hollow-ground, hole without keyway

Advantage:

- innovative cutting geometry with large chip space plus taper tap and third tap ensures cutting distribution and increases cutting performance
- top-quality cutting material for extremely demanding requirements in terms of service life
- universal use for a multitude of applications



Art. no.	14008 515
Brand	ORION
Manufacturer Part Number	14008515
Tooth shape	C
Cutting material	HSS
Thickness of cutting edge	2.5 mm
Tolerance of cutting edge diameter	js15
Tolerance of cutting edge thickness	js11
Tolerance of hole diameter	H7
Cutting edge diameter	63 mm
Bore diameter	16 mm
Number of teeth	32 PCS
DIN	1838
Form	C, extra narrow
Gross Weight	0.052 kg
Product Group	1QK

EAN

4039247080106