

STFC boring bar HSS positive, left-hand

For longitudinal turning with TC indexable insert

ATORN[®]

Application


For longitudinal and copy turning with TC indexable insert 60°.

Version

- Precision-made boring bar, **HSS**, with internal cooling, type T, attack angle 90°, tip angle 60°, clearance angle 7°

Advantage

- Three-cutter geometry reduces the costs per cutter
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



Art. No.	17850 092
ISO name	AH 16 Q STFC R/L 11
Min. bore diameter	18 mm
Shaft diameter	16 mm
Cutting edge height	7.5 mm
Clearance length	25 mm
Length	180 mm
Clamping surface height	15 mm
Programming size	11 mm
Suitable for indexable inserts	TC.. 1102..
Tool design	Left
DIN	8024

EAN-Code

4050293347562