

## Drawer with full extension, load capacity 100 kg

For empty housing of sliding-door cabinet no. 50051 900 and 910

### Application:

For customisation of empty housing for sliding-door cabinet no. 50051 900 and 910

### Execution:

- Made of steel sheet metal with a reinforced, perforated bottom (25 mm perforated grid)
- Runs on Delrin rollers in rails which are suspended in the housing with push-fit fastenings
- Inner sides slotted all around, for attaching and fixing individual items
- Equipped with aluminium handle strip, paper and cellophane strips and lateral cover caps
- SOFT-CLOSE AUTOMATIC for smooth closing of drawers without noise see no. 50392 005.



<b>Art. no.</b>	<b>50051 545</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50051545
<b>Drawer front height</b>	180 mm
<b>Drawer cabinet height</b>	130 mm
<b>Mount height</b>	130 mm
<b>Drawer width (inner dimension)</b>	600 mm
<b>Drawer depth (inner dimension)</b>	450 mm
<b>Drawer surface</b>	0.27 m <sup>2</sup>
<b>Pullout type</b>	Full extension
<b>Load-carrying capacity</b>	100 kg
<b>Material</b>	Sheet steel
<b>Colour of front</b>	Optional
<b>Box colour</b>	Basalt grey RAL 7012
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	13.600 kg
<b>Product Group</b>	501

### EAN

403924746945 1