

Vishay Semiconductors

High Intensity LED in Ø 3 mm Tinted Diffused Package



DESCRIPTION

This LED contains the double heterojunction (DH) GaAlAs on GaAs technology.

This deep red LED can be utilized over a wide range of drive current. It can be DC or pulse driven to achieve desired light output.

The device is available in a 3 mm tinted diffused package.

PRODUCT GROUP AND PACKAGE DATA

Product group: LEDPackage: 3 mm

Product series: standard
Angle of half intensity: ± 40°

FEATURES

- Exceptional brightness
- · Very high intensity even at low drive currents
- · Wide viewing angle
- · Low forward voltage
- 3 mm (T-1) tinted diffused package
- · Deep red color
- · Categorized for luminous intensity
- · Outstanding material efficiency

 Material categorization: for definitions of compliance please see www.vishay.com/doc?99912





RoHS

HALOGEN FREE

GREEN (5-2008)

APPLICATIONS

- · Bright ambient lighting conditions
- Battery powered equipment
- · Indoor and outdoor information displays
- Portable equipment
- · Telecommunication indicators
- General use

PARTS TABLE														
PART	COLOR	LUMINOUS INTENSITY (mcd)			at I _F	WAVELENGTH (nm)		at I _F	FORWARD VOLTAGE (V)		at I _F	TECHNOLOGY		
		MIN. TYP. MAX.	(IIIA)	MIN.	TYP.	MAX.	(IIIA)	MIN.	TYP.	MAX.	(IIIA)			
TLDR4400	Red	25	45	-	20	-	648	-	20	-	1.8	2.2	20	GaAlAs on GaAs

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified) TLDR4400						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Reverse voltage		V _R	6	V		
DC forward current	T _{amb} ≤ 60 °C	I _F	50	mA		
Surge forward current	t _p ≤ 10 μs	I _{FSM}	1	Α		
Power dissipation	T _{amb} ≤ 60 °C	P _V	100	mW		
Junction temperature		Tj	100	°C		
Operating temperature range		T _{amb}	-40 to +100	°C		
Storage temperature range		T _{stg}	-55 to +100	°C		
Soldering temperature	t ≤ 5 s, 2 mm from body	T _{sd}	260	°C		
Thermal resistance junction/ambient		R _{thJA}	400	K/W		



www.vishay.com Vishay Semiconductors

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25 ^{\circ}C$, unless otherwise specified) TLDR4400, RED						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity (1)	I _F = 20 mA	I _V	25	45	-	mcd
Luminous intensity	I _F = 1 mA	I _V	-	2		mcd
Dominant wavelength	I _F = 20 mA	λ_d	=	648	-	nm
Peak wavelength	I _F = 20 mA	λρ	=	650	-	nm
Spectral line half width	I _F = 20 mA	Δλ	-	20	-	nm
Angle of half intensity	I _F = 20 mA	φ	=	± 40	-	deg
Forward voltage	I _F = 20 mA	V _F	-	1.8	2.2	V
Reverse current	V _R = 6 V	I _R	-	-	10	μΑ
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	30	=	pF

Note

⁽¹⁾ In one packing unit $I_{Vmin.}/I_{Vmax.} \le 0.5$.

LUMINOUS INTENSITY CLASSIFICATION							
GROUP	LIGHT INTENSITY (mcd)						
STANDARD	MIN.	MAX.					
T	25	50					
U	40	80					
V	63	125					
W	100	200					
X	130	260					
Y	180	360					
Z	240	480					

Note

 Luminous intensity is tested at a current pulse duration of 25 ms and an accuracy of ± 11 %.

The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each bag (there will be no mixing of two groups on each bag).

In order to ensure availability, single brightness groups will not be orderable.

In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped on any one bag.

In order to ensure availability, single wavelength groups will not be orderable.

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature for InGaN





Fig. 2 - Forward Current vs. Pulse Length








Fig. 3 - Relative Luminous Intensity vs. Angular Displacement




Fig. 6 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 7 - Relative Luminous Intensity vs. Forward Current




Fig. 5 - Relative Luminous Intensity vs. Ambient Temperature





Fig. 8 - Relative Intensity vs. Wavelength




Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters







technical drawings according to DIN specifications

Drawing-No.: 6.544-5264.01-4

Issue: 4; 28.07.14



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000