


Item no.: 733-342
 Product description: Male header (for PCBs) Straight solder pin 0.8 x 0.8 mm 12-pole Pin spacing 2.5 mm / 0.098 in 100% protected against mismatching Vertical PCB mounting with closed end



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Weight	1.65 g
Color	light grey
pole count	12
Height	8.9 mm
Height	0.35 in
Width	32.5 mm
Width	1.28 in
Depth	7.8 mm
Depth	0.307 in
Pin spacing from	2.5 mm
Pin spacing from	0.098 in
Rating based on	IEC/EN 60664-1
Overvoltage category EN I	III
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Overvoltage category EN II	II

Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A



Overvoltage category EN III	III
Degree of pollution	3
Rated voltage EN	80 V
Rated surge voltage	2.5 kV
Nominal current	6 A
Solder pin length [mm]	4.6 mm
Solder pin width A [mm]	0.8 mm
Solder pin width B [mm]	0.8 mm
Diameter of drilled hole [mm]	1.1 mm
Tolerance of drilled hole diameter [mm]	0.1 mm
Material group	I
Insulating material	PA 6.6
Temperature stability	-60 °C to +100 °C
Flammability category, based on UL 94	V0
Contact material	Electrolytic copper (Ecu)
Contact plating	tin-plated



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
733-342	ABS	04-HG469925/1-PDA	250	4	0,5-1,5
733-342	BV	11915/A0	250	10	0,5-1,5
733-342	CCA	NL5640	250	4	0,5-1,5
733-342	CSA	154112-1465035	150	4	28-20
733-342	DNV	E-9218	250	10	0,5-1,5
733-342	GL	17296-00HH	250	10	0,5-1,5
733-342	KEMA	2077592.01	250	4	0,5-1,5
733-342	LR	96/20035	250	6	0,5-1,5
733-342	RMR	11130002	250	10	0,5-1,5
733-342	UR	E45171	250	4	
733-342	UR	E45172	150	4	28-20

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected