



2628G

ERGO™ Combination Pliers with Dual-Component Handle and Phosphate Finish

PRODUCT DETAILS

- ERGO™ handles with two-component combination: thermoplastic surface on tough polypropylene gives superior grip
- Combination pliers developed according to the scientific ERGO™ process
- Suitable for cutting Fe+ and piano wire
- Equipped with a return spring featuring an on/off function
- High-performance alloy steel
- Phosphate finish, anti-corrosion treated
- Maximum comfort with minimum effort due to the ergonomic design
- Comfortable two-component handles giving an excellent grip
- Greater leverage and cutting capacity because of the position of the joint
- Shaped head for better access with specially designed edges for cutting piano wire and spring steel
- Self-opening handles when spring activated
- Cutting edge specially designed to cut harder material such as piano wire
- Distance from the joint to the centre of the cutting edges is reduced: giving greater leverage and increased cutting capacity
- Gripping surfaces particularly suited for gripping round and flat material



Follow the Fish!



PRODUCT ATTRIBUTES

| Product | ✘ | ✘ | ✘ | ✘ | ✘ | ✘ | ✘ | ✘ | ✘ | ✘ |
|---------------------|--------|-------|---------|--------|--------|---------|-------|--------|--------|-------|
| 2628 G-160 | 160 mm | 32 mm | 22 mm | 9,8 mm | 3,5 mm | 9.8 mm | 12 mm | 2.0 mm | 1.8 mm | 190 g |
| 2628 G-180 | 180 mm | 36 mm | 24 mm | 11 mm | 4 mm | 11.0 mm | 14 mm | 2.5 mm | 2.0 mm | 240 g |
| 2628 G-200 | 200 mm | 39 mm | 27,9 mm | 12 mm | 4 mm | 12.0 mm | 16 mm | 3.0 mm | 2.5 mm | 300 g |
| 2628 G-160IP | 160 mm | 33 mm | 23 mm | 10 mm | 4 mm | 10 mm | 12 mm | 2.0 mm | 1.8 mm | 190 g |
| 2628 G-180IP | 180 mm | 36 mm | 24 mm | 11 mm | 4 mm | 11.0 mm | 14 mm | 2.5 mm | 2.0 mm | 240 g |
| 2628G-200IP | 200 mm | 39 mm | 27,9 mm | 12 mm | 4 mm | 12.0 mm | 16 mm | 3.0 mm | 2.5 mm | 300 g |

