


High Voltage Thin Film Flat Chip Resistors



TNPV e3 precision thin film flat chip resistors are the perfect choice for most fields of modern electronics where the highest reliability and stability at high operating voltages are of major concern. Typical applications include industrial and automotive inverters, voltage measurement systems as implemented in battery management systems, and test and measuring equipment.

FEATURES

- High operating voltage U_{max}, up to 1000 V
- Low voltage coefficient < 1 ppm/V





- Superior moisture resistivity (85 °C; 85 % RH)
- AEC-Q200 qualified
- Sulfur resistance verified according to ASTM B 809
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Industrial and automotive inverters
- Battery management system
- · Test and measuring equipment

| TECHNICAL SPECIFICATIONS | | | | |
|--|--|-----------------------------------|--|--|
| DESCRIPTION | TNPV1206 e3 | TNPV1210 e3 | | |
| Imperial size | 1206 | 1210 (1) | | |
| Metric size code | RR3216M | RR3225M ⁽¹⁾ | | |
| Resistance range | 160 kΩ to 2 MΩ | 121 k Ω to 3.01 M Ω | | |
| Resistance tolerance | ± 1 %; ± 0.5 %; ± 0.1 % | | | |
| Temperature coefficient | ± 50 ppm/K; ± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K | | | |
| Voltage coefficient c | <1 | ppm/V | | |
| Rated dissipation, P ₇₀ (2) | 0.25 W | 0.33 W | | |
| Maximum operating voltage, $U_{\rm max.}$ AC _{RMS} or DC ⁽³⁾ | 700 V | 1000 V | | |
| Permissible film temperature, $g_{\text{F max.}}^{(2)}$ | 155 °C | | | |
| Operating temperature range | -55 °C to 125 °C (155 °C) | | | |

Notes

- (1) Size not specified in EN 140401-801
- (2) Please refer to APPLICATION INFORMATION below
- (3) Application-specific safety requirements may set limitations to the applicability of the specified voltage

APPLICATION INFORMATION

The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials may be required to maintain the reliability of the assembly.

These resistors do not feature a lifetime limitation when operated within the limits of rated dissipation, permissible operating voltage, and permissible film temperature. However, the resistance typically increases due to the resistor's film temperature over operating time, generally known as drift. The drift may exceed the stability requirements of an individual application circuit and thereby limits the functional lifetime. The designer may estimate the performance of the particular resistor application or set certain load and temperature limits in order to maintain a desired stability.


| MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION | | | | | |
|---|-------------|-----------------------------------|--|--|--|
| OPERATION MODE | | STANDARD | | | |
| Rated dissipation, P_{70} | TNPV1206 e3 | 0.25 W | | | |
| nated dissipation, F ₇₀ | TNPV1210 e3 | 0.33 W | | | |
| Applied maximum film temperature, ϑ_{F} max. | | 125 °C | | | |
| | TNPV1206 e3 | 160 k Ω to 2 M Ω | | | |
| | TNPV1210 e3 | 121 k Ω to 3.01 M Ω | | | |
| Max. resistance change at P_{70} for resistance range $\Delta R/R$, after: | 1000 h | ≤ 0.05 % | | | |
| | 8000 h | ≤ 0.10 % | | | |
| | 225 000 h | ≤ 0.30 % | | | |

| TEMPERATURE COEFFICIENT AND RESISTANCE RANGE | | | | | | | |
|--|------------|------------|-----------------------------------|-----------|--|--|--|
| TYPE/SIZE | TCR | RESISTANCE | E-SERIES | | | | |
| | ± 50 ppm/K | ± 1 % | | E24; E96 | | | |
| | ± 25 ppm/K | ± 0.5 % | | | | | |
| TNPV1206 e3 | | ± 0.1 % | 160 k Ω to 2.0 M Ω | E24; E192 | | | |
| | ± 15 ppm/K | ± 0.1 % | | | | | |
| | ± 10 ppm/K | ± 0.1 % | | | | | |
| TNPV1210 e3 | ± 50 ppm/K | ± 1 % | 121 kΩ to 3.01 MΩ | E24; E96 | | | |
| | . 05 (1/ | ± 0.5 % | 121 K52 tO 3.01 W52 | | | | |
| | ± 25 ppm/K | ± 0.1 % | | E24; E192 | | | |
| | ± 15 ppm/K | ± 0.1 % | 121 k Ω to 2.13 M Ω | E24, E192 | | | |
| | ± 10 ppm/K | ± 0.1 % | | | | | |

| PACKAGING | | | | | | | |
|--|----------|---------------------|--------------------------------|------|------|--------------|--|
| TYPE/SIZE CODE QUANTITY PACKAGING STYLE WIDTH PITCH REEL DIAME | | | | | | | |
| TNPV1206 e3 TNPV1210 e3 | E52 = EN | 1000 ⁽¹⁾ | Paper tape acc. IEC 60286-3 | | | 180 mm / 7" | |
| | ET1 = EA | 5000 | | 8 mm | 4 mm | | |
| | ET6 = EC | 20 000 | Type 1a | | | 330 mm / 13" | |

Note

 $^{^{(1)}}$ 1000 pieces packaging is available only for precision resistors with tolerance \pm 0.1 %



Note

• Products can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION

DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of special metal alloy is deposited on a high grade ceramic substrate (Al₂O₃) and conditioned to achieve the desired temperature coefficient. Specially designed inner contacts are deposited on both sides. A special laser is used to achieve the target value by smoothly cutting a meander groove in the resistive layer without damaging the ceramics. The resistor elements are covered by a unique protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure and optical inspection performed on 100 % of the individual chip resistors. This includes full screening for the elimination of products with a potential risk of early life failures according to EN 140401-801, 2.1.2.2. Only accepted products are laid directly into the paper tape in accordance with **IEC 60286-3** (1).

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds, and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. The immunity of the plating against tin whisker growth has been proven under extensive testing.

All products comply with the **IEC 62474**, Material Declaration for Products of and for the Electrotechnical Industry. The dedicated database ⁽²⁾, that lists declarable substances, ensures full compliance with the following directives:

- 2000/53/EC End of Vehicle life Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the use of Hazardous Substances directive (RoHS)
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

The resistors are halogen-free according to JEDEC® JS709A definition. Solderability is specified for 2 years after production or re-qualification. The permitted storage time is 20 years.

RELATED PRODUCTS

For products with ultra precision specification see the datasheet:

 TNPU e3 - Ultra Precision Thin Film Flat Chip Resistors (www.vishay.com/doc?28779)

For products with high stability specification see the datasheet:

 TNPW e3 - High Stability Thin Film Flat Chip Resistors (www.vishay.com/doc?28758)


Note

(1) The quoted IEC standards are also released as EN standards with the same number and identical contents

(2) IEC 62474 database can be found at http://std.iec.ch/iec62474




FUNCTIONAL PERFORMANCE



Derating

Note

 The solid line is based on IEC/EN reference test conditions which is considered as standard mode. However, above that the maximum permissible film temperature is 155 °C (dashed line)




Resistance Value in Ω

Nominal Operating Voltage


Note

The permissible operating voltage U_{max} equals the rated voltage \(\sqrt{P}_{70} \times R \). For ambient temperatures above 70 °C power derating must be considered





Maximum Pulse Load $\hat{P}_{i, max.}$ Single Pulses



Maximum Pulse Voltage $\hat{U}_{i, max.}$



TEST AND REQUIREMENTS

All tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-801, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-801. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA / ECA-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, where upon the following values are applied:

Temperature: 15 °C to 35 °C Relative humidity: 45 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar)

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days).

The components are mounted for testing on printed circuit boards in accordance with EN 60115-8, 2.4.2, unless otherwise specified.

| TEST PR | TEST PROCEDURES AND REQUIREMENTS | | | | | | |
|----------------------|----------------------------------|---|---|--|--|--|--|
| EN 60115-1 CLAUSE | | | PROCEDURE | REQUIREMENTS PERMISSIBLE CHANGE (ΔR) | | | |
| | | | Stability for product type: | | | | |
| | | | TNPV1206 e3 TNPV1210 e3 | | | | |
| 4.5 | - | Resistance | - | ± 1 %; ± 0.5 %; ± 0.1 % | | | |
| 4.8.4.2 | - | Temperature coefficient | At (20 / -55 / 20) °C and (20 / 125 / 20) °C | ± 50 ppm/K; ± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K | | | |
| 4.25.1 | - | Endurance | U = U _{max.} ; 1.5 h on; 0.5 h off; | (0.05.0(B) | | | |
| | | at 70 °C | 70 °C; 1000 h | ± (0.05 % R) | | | |
| | | | 70 °C; 8000 h | ± (0.1 % R) | | | |
| 4.25.3 | - | Endurance at upper category temperature | 125 °C; 1000 h 155 °C; 1000 h | ± (0.05 % R) ± (0.1 % R) | | | |
| 4.24 | 78 (Cab) | Damp heat, steady state | (40 ± 2) °C; 56 days; (93 ± 3) % RH; $U = 0.1 \times U_{\text{max.}}$ | ± (0.1 % R) | | | |
| 4.19 | 14 (Na) | Rapid change of temperature | 30 min at LCT and 30 min at UCT; LCT = -55 °C; UCT = 125 °C; 1000 cycles | ± (0.1 % R) | | | |
| 4.13 | - | Short time overload | $U = 2 \times U_{\text{max.}};$ 5 s | ± (0.05 % R) | | | |
| 4.27 | - | Single pulse high voltage overload | Severity no. 4: $U = 2 \times U_{\text{max.}};$ 10 pulses 10 µs/700 µs | ± (0.1 % R) | | | |
| 4.39 | - | Periodic electric overload | $U = 2 \times U_{\text{max}};$ 0.1 s on; 2.5 s off; 1000 cycles | ± (0.1 % R) | | | |
| 4.22 | 6 (Fc) | Vibration | Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s ² ; 7.5 h | ± (0.05 % R) | | | |



www.vishay.com

Vishay Draloric


| TEST PR | TEST PROCEDURES AND REQUIREMENTS | | | | | | |
|----------------------|-----------------------------------|--|--|--|--|--|--|
| EN 60115-1 CLAUSE | IEC 60068-2 (1) TEST METHOD | TEST | PROCEDURE | REQUIREMENTS PERMISSIBLE CHANGE ($\triangle R$) | | | |
| | | | Stability for product type: | | | | |
| | | | TNPV1206 e3 TNPV1210 e3 | | | | |
| 4.38 | - | Electrostatic discharge (Human Body Model) | IEC 61340-3-1 ⁽¹⁾ ; 3 pos. + 3 neg. discharges; 6 kV | ± (0.5 % R) | | | |
| | | | Solder bath method; SnPb40; non-activated flux (215 ± 3) °C; (3 ± 0.3) s | Good tinning (≥ 95 % covered); | | | |
| 4.17.2 | 58 (Td) | Solderability | Solder bath method; SnAg3Cu0.5 or SnAg3.5; non-activated flux (235 ± 3) °C; (2 ± 0.2) s | no visible damage | | | |
| | | Resistance to | Solder bath method; (260 ± 5) °C; (10 ± 1) s | | | | |
| 4.18.2 | 58 (Td) | soldering heat | Reflow method 2 (IR/forced gas convection); (260 ± 5) °C; (10 ± 1) s | ± (0.02 % <i>R</i>) | | | |
| 4.29 | 45 (XA) | Component solvent resistance | Isopropyl alcohol; 50 °C; method 2 | No visible damage | | | |
| 4.30 | 45 (XA) | Solvent resistance of marking | Isopropyl alcohol; 50 °C; method 1, toothbrush | No visible damage | | | |
| 4.32 | 21 (Ue ₃) | Shear (adhesion) | 45 N | No visible damage | | | |
| 4.33 | 21 (Ue ₁) | Substrate bending | Depth 2 mm, 3 times | ± (0.05 % R) no visible damage, no open circuit in bent position | | | |
| 4.35 | - | Flammability | IEC 60695-11-5 ⁽¹⁾ , needle flame test; 10 s | No burning after 30 s | | | |
| 4.37 | 67 (Cy) | Damp heat, steady state, accelerated | (85 ± 2) °C; (85 ± 5) % RH; <i>U</i> = 0.3 x <i>U</i> _{max} .; 1000 h | ± (0.25 % R) | | | |

Note

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents




DIMENSIONS



| DIMENSIONS AND MASS | | | | | | | |
|---------------------|-------------|-------------------------------------|--------------|------------|----|--|--|
| TYPE | H (mm) | T _t /T _b (mm) | MASS (mg) | | | | |
| TNPV1206 e3 | 0.55 ± 0.10 | 3.2 + 0.1 / - 0.2 | 1.6 ± 0.15 | 0.5 ± 0.25 | 10 | | |
| TNPV1210 e3 | 0.60 ± 0.15 | 3.2 + 0.1 / - 0.2 | 2.45 ± 0.15 | 0.5 ± 0.25 | 16 | | |

SOLDER PAD DIMENSIONS



| RECOMMENDED SOLDER PAD DIMENSIONS | | | | | | | |
|-----------------------------------|---------------------------------|-----------|-----------|-----------|-----------|-----------|--|
| | REFLOW SOLDERING WAVE SOLDERING | | | | ì | | |
| TYPE | Y (mm) | X (mm) | G (mm) | Y (mm) | X (mm) | G (mm) | |
| TNPV1206 e3 | 0.9 | 1.7 | 2.0 | 1.1 | 1.7 | 2.3 | |
| TNPV1210 e3 | 0.9 | 2.5 | 2.0 | 1.1 | 2.5 | 2.3 | |

Note

 Utilization of the full specified operating voltage may require special considerations on the creepage and clearance distance between conductors at different potential levels



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.