

## Machine nut tap, M ISO 2X (6HX) 0° 357

For universal use up to 1000 N/mm<sup>2</sup>

**ATORN**<sup>®</sup>



### Application

For machining metric threads (cutting nuts or bridging cavities) in through holes on CNC or conventional machines in the steel, (stainless steel), NF metal and (cast) material groups up to a strength of 1000 N/mm<sup>2</sup>.

### Version

- Long design

### Advantage

- Very long thread section can bridge cavities between threads
- Universal use for maximum flexibility

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	16	11		9		18	18	15	18	15	15	13		16					

<b>Art. No.</b>	<b>13059 100</b>
<b>Type</b>	P MAX 1000
<b>Thread type</b>	Metric thread
<b>Thread type x nominal diameter</b>	M10
<b>Pitch</b>	1.5 mm
<b>Hole type</b>	Clearance hole ≤ 3xD
<b>Cutting material</b>	HSSE
<b>Surface</b>	Uncoated
<b>Tolerance of screw taps</b>	ISO 2X (6HX)
<b>Twist angle</b>	0°
<b>Shaft diameter</b>	7 mm
<b>Application type/machine type</b>	CNC, Conventional
<b>Core hole diameter</b>	8.5 mm
<b>Coolant supply</b>	External
<b>Length</b>	140 mm
<b>Shank square</b>	5.5 mm
<b>Cutting speed (steel 1000) suitability</b>	1
<b>Cutting speed (steel 1300) suitability</b>	3
<b>Overall stainless steel suitability</b>	3
<b>fitness not iron total</b>	1
<b>fitness Titan/Nickel/Super total</b>	3
<b>Cutting speed (cast) suitability</b>	2
<b>Cutting speed (hard 55) suitability</b>	3
<b>Cutting speed (hard 65) suitability</b>	3
<b>DIN</b>	357

### EAN-Code

4050293016857