

Surface chuck (Weldon) ISO 7388-1

KKB = resealable coolant bores

ATORN[®]

Application

For clamping tools with straight shank and clamping surface in accordance with DIN 1835 B.

Version

- alloyed case-hardening steel with tensile strength at the core of at least 950 N/mm²
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080
- Concentricity of the tool chuck, internal taper to the clamping diameter ≤ 0.005 mm
- All functional surfaces machined

Delivery

Includes clamping screw



Art. no.	23157 937
Tool holding device	SK 50
Clamping diameter	6 mm
Projecting length	100 mm
Outer diameter	25 mm
Clearance length to collar	81 mm
Balancing quality	G 2.5 at 25 rpm
Form	AD/AF

EAN-Code

4050293707533