

4820HL.B



Models Versions

| Models | Versions |
|-----------|-------------------|
| 4820HL.B | black w/foam |
| 4820HL.BE | black empty |
| 4820HL.G | mil. green w/foam |
| 4820HL.GE | mil. green empty |
| 4820HL.O | orange w/foam |
| 4820HL.OE | orange empty |

- Made of Copolymer Polypropylene compound
- Waterproof, resistant to chemicals, humidity, dust
- Resistant to harsh temperatures (-33°C / +90°C)
- Jam-free purge valve and latches
- Recommended for professional applications

- 100% made in Italy: Italian design and proven functionality
- First to achieve the new military standard qualifications
- Recognized as the most versatile case to customize
- Widest choice of accessories to customize your experience
- Incorporate a number of patented innovations

| Technical Features | | L | W | D | | |
|---|----|--------|-------|--------------------|-----|------|
| | | Length | Width | Depth | Lid | Base |
| Internal dim. | mm | 480 | 370 | 205 | 50 | 155 |
| External dim. | mm | 520 | 440 | 230 | | |
| Weight empty | | | | Kg 3,33 | | |
| Weight w/foam | | | | Kg 4,09 | | |
| Weight w/multi | | | | Kg --- | | |
| Volume | | | | lt 36,4 | | |
| Buoyancy | | | | Kg/max 24,8 | | |
| Temp. rating | | | | °C min -33 max +90 | | |
| Certifications | | | | | | |
| 2002/95/EC Conformity with the Directive 2002/95/EC | | | | | | |
| DEF STAN 81-41 (level J) | | | | | | |
| IP67 Dustproof - Waterproof | | | | | | |
| STANAG 4280 (edition 2) | | | | | | |

