

## Transverse drive shell end mill arbor DIN 6357 (face mill arbor)

With enlarged collar diameter, ISO-7388-1

**ATORN**<sup>®</sup>

### Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm<sup>2</sup>
- Internal coolant supply
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm
- max. concentricity < 0.005 mm
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080

### Delivery

includes key blocks and cutter retaining screw



<b>Art. no.</b>	<b>23162 192</b>
<b>Tool holding device</b>	SK 50
<b>Form</b>	AD
<b>Mandrel diameter</b>	16 mm
<b>Tap length</b>	17 mm
<b>Projecting length</b>	160 mm
<b>Outer diameter</b>	38 mm
<b>Balancing quality</b>	G 2.5 at 25 rpm
<b>Coolant supply</b>	Internal axial

### EAN-Code

4050293712261