



TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PA 6T
 COLOR: BLACK
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: GOLD
 QUALITY CLASS: 3 AS PER CECC 75 301-802
 PITCH: 2.00MM

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 125°C
 FLAMABILITY RATING: UL94-V0
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 2A MAX
 WORKING VOLTAGE: 250V AC
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC/MN
 CONTACT RESISTANCE: 20 mOHM MAX

STANDARD
 CERTIFIED E323964

SOLDERING
 REFLOW PROCESS ONLY

PACKAGING
 TUBE

DIMENSION
 A = 2.00 x (NB. PIN / 2 - 1)
 B = 2.00 x (NB. PIN / 2)

RoHS Compliant

G				PROJECTION:
F	26-JUL-13	MATERIAL	QL	
E	23-NOV-07	MODIFICATIONS	EC	
D	12-DEC-06	DRAW	EC	
C	31-MAR-04	LEAD FREE	JP	
B	19-MAR-04		JP	APPROVAL: RJ
A	28-AUG-98	PDF	JP	
REV	DATE	FILE	BY	

GENERAL TOLERANCE	
.X = +/- 0.2	
.XX = +/- 0.15	
UNIT: MM	DESCRIPTION: 2.00MM DUAL SMT PIN HEADER
SCALE:	
SHEET: 1/1	WERI PART NO: 6210 xx 21921
DRAW: PEARL	

SIZE
A4