



TEMPERATURE MONITORING RELAY PT100/1000,  
KTY83/84, NTC 3 SENSORS, 2 THRESH., DIGITAL -58  
DEGR. F TO 932 DEGR. F 24-240V AC/DC 2 X 1 CC +  
1 NC, WIDTH 45 MM SCREW CONNECTION

Figure similar


General technical data:		
<b>Type of voltage</b>		AC/DC
<b>Supply voltage frequency</b>		
<ul style="list-style-type: none"> <li>• 1 for auxiliary and control current circuit               <ul style="list-style-type: none"> <li>— Initial rated value</li> <li>— Final rated value</li> </ul> </li> </ul>	Hz	50
	Hz	60
<b>Control supply voltage</b>		
<ul style="list-style-type: none"> <li>• 1               <ul style="list-style-type: none"> <li>— with AC                   <ul style="list-style-type: none"> <li>— at 50 Hz Initial rated value</li> <li>— at 50 Hz Final rated value</li> <li>— at 60 Hz Initial rated value</li> <li>— at 60 Hz Final rated value</li> </ul> </li> <li>— for DC                   <ul style="list-style-type: none"> <li>— Initial rated value</li> <li>— Final rated value</li> </ul> </li> </ul> </li> </ul>	V	24
	V	240
	V	24
	V	240
	V	24
	V	240
<b>Number of measuring circuits</b>		3
<b>Number of NC contacts for auxiliary contacts</b>		0
<b>Number of NO contacts for auxiliary contacts</b>		1
<b>Number of CO contacts for auxiliary contacts</b>		2
<b>Product function</b>		
<ul style="list-style-type: none"> <li>• Fault storage</li> <li>• External reset</li> </ul>		Yes
		Yes
<b>Measurable Fahrenheit-temperature</b>		
<ul style="list-style-type: none"> <li>• initial value</li> </ul>	°F	-58

• Full-scale value	°F	932
Equipment marking acc. to DIN EN 61346-2		K
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		K
Ambient temperature during operation	°C	-25 ... +60

#### Mechanical data:

<b>Type of electrical connection</b>		
<ul style="list-style-type: none"> <li>• for auxiliary and control current circuit</li> <li>• Plug-in socket</li> </ul>		screw-type terminals Yes
<b>Design of the sensor connectable</b>		PT100/1000, KTY83/84, NTC (resistance sensors)
<b>Width</b>	mm	45
<b>Height</b>	mm	106
<b>Depth</b>	mm	91

#### Certificates/ approvals:

General Product Approval	Test Certificates	other	
	<a href="#">Special Test Certificate</a>	<a href="#">Environmental Confirmations</a>	<a href="#">Declaration of Conformity</a>

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RS20411GW50>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<http://support.automation.siemens.com/WW/view/en/3RS20411GW50/all>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RS20411GW50&lang=en>



last modified:



09.03.2015