

CIRCUIT BREAKER 400V 10KA, 3+N-POLE, D, 0.3A



Figure similar

Model		
product brand name		SENTRON
Product designation		Miniature circuit breakers
<b>Design of the product</b>		5SL miniature circuit breakers
General technical data		
<b>Number of poles</b>		4
<b>Number of poles / Note</b>		3P+N
<b>Tripping characteristic class</b>		D
<b>circuit-breaker / Design</b>		5SL4
<b>Mechanical service life (switching cycles) / typical</b>		10 000
<b>Overvoltage category</b>		3
Voltage		
<b>Insulation voltage</b>		
<ul style="list-style-type: none"> <li>with multi-phase operation / with AC / Rated value</li> </ul>	V	440
Supply voltage		
Supply voltage frequency / Rated value	Hz	50
Protection class		
<b>Protection class IP</b>		IP20, with connected conductors
<b>Energy limiting class</b>		3
Switching capacity		
<b>Switching capacity current</b>		
<ul style="list-style-type: none"> <li>acc. to EN 60898 / Rated value</li> </ul>	kA	10

- acc. to IEC 60947-2 / Rated value

kA	10
----	----

### Dissipation

<b>Active power loss</b>		
<ul style="list-style-type: none"> <li>• for rated value of the current / with AC / in hot operating state / per pole</li> </ul>	W	0.91

### Electricity

rated current I <sub>n</sub> / IEC, DIN/VDE / at 40 Cel	A	0.28
Current / with AC / Rated value	A	0.3

### Main circuit

<b>Operating voltage</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	V	24
<ul style="list-style-type: none"> <li>• for DC / Rated value / maximum</li> </ul>	V	60
<ul style="list-style-type: none"> <li>• with multi-phase operation / with AC / maximum</li> </ul>	V	440

### Product details

Product feature / Touch protection		Yes
<b>Product property</b>		
<ul style="list-style-type: none"> <li>• halogen-free</li> </ul>		Yes
<ul style="list-style-type: none"> <li>• sealable</li> </ul>		Yes
<ul style="list-style-type: none"> <li>• silicon-free</li> </ul>		Yes
Product expansion / can be installed / supplementary devices		Yes

### Product function

Product function / neutral conductor switching		Yes
--	--	-----

### Number

<b>Number of test cycles / for environmental testing / acc. to IEC 60068-2-30</b>		6
---	--	---

### Connections

<b>Connectable conductor cross-section / stranded</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	mm <sup>2</sup>	0.75
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	mm <sup>2</sup>	35
<b>Connectable conductor cross-section</b>		
<ul style="list-style-type: none"> <li>• solid</li> </ul>		
<ul style="list-style-type: none"> <li>— minimum</li> </ul>	mm <sup>2</sup>	0.75
<ul style="list-style-type: none"> <li>— maximum</li> </ul>	mm <sup>2</sup>	35
<ul style="list-style-type: none"> <li>• finely stranded / with core end processing</li> </ul>		
<ul style="list-style-type: none"> <li>— minimum</li> </ul>	mm <sup>2</sup>	0.75
<ul style="list-style-type: none"> <li>— maximum</li> </ul>	mm <sup>2</sup>	25
<b>Tightening torque / with screw-type terminals</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	N·m	2.5
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	N·m	3

Mechanical Design		
Height	mm	90
Width	mm	72
Depth	mm	76
mounting position		any
Installation depth	mm	70
Number of width units		4

Environmental conditions		
Influence of the surrounding temperature		+55 °C, max. 95% humidity
Ambient temperature		
• minimum	°C	-25
• maximum	°C	55
• during storage / minimum	°C	-40
• during storage / maximum	°C	75

Certificates		
Equipment marking		
• acc. to DIN EN 61346-2		F
• acc. to DIN EN 81346-2		F

General Product Approval	Declaration of Conformity
--------------------------	---------------------------



other

[other](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SL46148>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/5SL46148/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SL46148](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SL46148)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015