



DEBUR AND BREAK SHARP EDGES

DO NOT SCALE DRAWING

REVISION



PART No.	"A"
TRLCBSM-2-01	3.2
TRLCBSM-9-01	14.3

C	Pt.No TABLE ADDED M.E. 01/07/14
B	DRG No.CHANGED M.E. 18/06/14
A	DRAWN 01/11/13

- NOTES
- MATERIAL:PA66 UL94 V2;PA66 UL94 V0;
  - COLOR:NATURAL;
  - ROHS Compliant;
  - TOP Hole: $\phi 3.18 \pm 0.08\text{mm}$   
Panel Thickness:0.79-1.98mm.
  - Bottom Hole: $\phi 3.18 \pm 0.08\text{mm}$   
Panel Thickness:1.57mm.



DESIGN RIGHT. TR FASTENINGS LTD, 2003  
UNDER NO CIRCUMSTANCES MUST THIS  
DRAWING BE COPIED OR DISCLOSED,  
WITHOUT FIRST OBTAINING WRITTEN  
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN MILLIMETERS  
SURFACE FINISH:  
TOLERANCES:

ISO 2768 m	
NAME	DATE
DRAWN MARTIN ELLIOTT	01/11/13
CHK'D	
APP'VD	

CUSTOMER PART No

MATERIAL:  
SEE NOTES

HEAT TREATMENT  
N/A

FINISH:  
N/A

TITLE:  
LOCKING CIRCUIT  
BOARD SUPPORT

DWG NO.  
TRLCBSM-X-01

A3