## Interface Cable for CSMH/CSHH

## ZDNV010


Part Number




## **Technical Data**

Mechanical Data	
Connection 1	Plug, straight
Connection mode 1	USB-A, 4-pin
Connection 2	Plug, straight
Connection mode 2	RJ50, 10-pin
Cable Length	2,4 m
Cable Jacket Material	PVC
Material Wire Insulation	PUR
Screened	yes
Packaging unit	1 Piece
Connection Diagram No.	S100
Connection Equipment No.	45 83

## • PVC, straight





Leger	nd	PT	Platinum measuring resistor	ENAR5422	Encoder A/Ā (TTL)
+	Supply Voltage +	nc	not connected	ENBRS422	Encoder B/B (TTL)
-	Supply Voltage 0 V	U	Test Input	ENA	Encoder A
~	Supply Voltage (AC Voltage)	Ū	Test Input inverted	ENB	Encoder B
Α	Switching Output (NO)	W	Trigger Input	Amin	Digital output MIN
Ā	Switching Output (NC)	W -	Ground for the Trigger Input	Амах	Digital output MAX
V	Contamination/Error Output (NO)	0	Analog Output	Аок	Digital output OK
⊽	Contamination/Error Output (NC)	0-	Ground for the Analog Output	SY In	Synchronization In
E	Input (analog or digital)	BZ	Block Discharge	SY OUT	Synchronization OUT
Т	Teach Input	Awv	Valve Output	OLT	Brightness output
Z	Time Delay (activation)	а	Valve Control Output +	М	Maintenance
S	Shielding	b	Valve Control Output 0 V	rsv	reserved
RxD	Interface Receive Path	SY	Synchronization	Wire Co	lors according to DIN IEC 757
TxD	Interface Send Path	SY-	Ground for the Synchronization	BK	Black
RDY	Ready	E+	Receiver-Line	BN	Brown
GND	Ground	S+	Emitter-Line	RD	Red
CL	Clock	±	Grounding	OG	Orange
E/A	Output/Input programmable	SnR	Switching Distance Reduction	YE	Yellow
•	IO-Link	Rx+/-	Ethernet Receive Path	GN	Green
PoE	Power over Ethernet	Tx+/-	Ethernet Send Path	BU	Blue
IN	Safety Input	Bus	Interfaces-Bus A(+)/B(-)	VT	Violet
OSSD	Safety Output	La	Emitted Light disengageable	GY	Grey
Signal	Signal Output	Mag	Magnet activation	WH	White
BI_D+/-	Ethernet Gigabit bidirect, data line (A-D)	RES	Input confirmation		Pink
EN0RS42	2 Encoder 0-pulse 0-0 (TTL)	EDM	Contactor Monitoring	GNYE	Green/Yellow