

## Miniature cutting insert, type AG HC5640 for inner grooves

**ATORN®**

### Application

For inner grooves in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

### Version

- solid carbide cutting insert with inner cooling

### Advantage

- tough cemented carbide type for broad application field
- stable geometry for cutting insert
- ideal for use with inefficient machines and unstable cutting conditions



<b>Art. No.</b>	<b>17129 156</b>
<b>ISO name</b>	AG
<b>Shaft diameter</b>	6 mm
<b>Length</b>	51 mm
<b>Clearance length</b>	15 mm
<b>Programming size 2</b>	1.4 mm
<b>Recessing width</b>	2 mm
<b>Programming size</b>	2.8 mm
<b>Min. bore diameter</b>	6.1 mm
<b>Machining direction</b>	Right
<b>Carbide type</b>	HC5640
<b>Material to be processed</b>	Steel, Stainless steel, Non-ferrous metal, Cast metal

### EAN-Code

4050293266870