

Hinged frame HMC 16B f. 4 modules (a..d)



Part number	09 14 216 0313
Specification	Hinged frame HMC 16B f. 4 modules (ad)
HARTING eCatalogue	https://b2b.harting.com/09142160313

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series	Han-Modular [®]
Type of accessory	Hinged frame
Description of the accessory	HMC version for 4 modules a d
Features	Conductor cross-section PE (power side) 4 10 mm² Conductor cross-section PE (signal side) 1 2.5 mm²

Version

Size	16 B

Technical characteristics

Stripping length	8 10 mm
Limiting temperature	-40 +125 °C
Mating cycles with other HMC components	≥10,000

Material properties

Material	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	564b7d75-7bf6-4cfb-acb1-2168eb61b675
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

2
67.8 g
Germany
85389099
5713140021549
EC002312
27440206 Module carrier frame for industrial connectors