

## SVXC solid carbide boring bar, positive left

For longitudinal and copy turning with VC indexable insert

**ATORN**<sup>®</sup>



### Application

For longitudinal and copy turning with VC indexable insert 55°

### Execution

- Precision-manufactured boring bar, **solid carbide**, with internal cooling, type V, attack angle 113°, tip angle 35°, clearance angle 7°

### Advantage

- Slender geometry for longitudinal and copy turning
- Positive geometry for the body ensures low cutting forces

<b>Art. No.</b>	<b>17827 500</b>
<b>ISO name</b>	E 16M SVXC R/L 07
<b>Min. bore diameter</b>	19.5 mm
<b>Shaft diameter</b>	16 mm
<b>Cutting edge height</b>	9.5 mm
<b>Clearance length</b>	55 mm
<b>Length</b>	150 mm
<b>Clamping surface height</b>	15 mm
<b>Programming size</b>	11 mm
<b>Suitable for indexable inserts</b>	VC.. 0702..
<b>Tool design</b>	Left
<b>DIN</b>	8024

### EAN-Code

4050293390896