

Drawer with full extension, load capacity 100 kg

For empty housing of sliding-door cabinet no. 50051 900 and 910

Application:

For customisation of empty housing for sliding-door cabinet no. 50051 900 and 910

Execution:

- Made of steel sheet metal with a reinforced, perforated bottom (25 mm perforated grid)
- Runs on Delrin rollers in rails which are suspended in the housing with push-fit fastenings
- Inner sides slotted all around, for attaching and fixing individual items
- Equipped with aluminium handle strip, paper and cellophane strips and lateral cover caps
- SOFT-CLOSE AUTOMATIC for smooth closing of drawers without noise see no. 50392 005.



Art. no.	50051 525
Brand	HK
Manufacturer Part Number	50051525
Drawer front height	120 mm
Drawer cabinet height	100 mm
Mount height	100 mm
Drawer width (inner dimension)	600 mm
Drawer depth (inner dimension)	450 mm
Drawer surface	0.27 m ²
Pullout type	Full extension
Load-carrying capacity	100 kg
Material	Sheet steel
Colour of front	Optional
Box colour	Basalt grey RAL 7012
Surface	Powder-coated
Gross Weight	12.000 kg
Product Group	501

EAN

4039247469413