



Actinic BL PL-S/PL-L

PL-L 18W/10/4P 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Mechanical and Housing	
Cap-Base	2G11 [2G11]	Bulb Shape	2xT16
Light Technical		Product Data	
Color Code	10	Full product code	871150026018540
Color Designation	Ultra Violet A	Order product name	PL-L 18W/10/4P 1CT/25
Chromaticity Coordinate X (Nom)	228	Order code	927903001007
Chromaticity Coordinate Y (Nom)	215	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	25
Power Consumption	18 W	Material number (12NC)	927903001007
Lamp Current (Nom)	0.375 A	Full product name	PL-L 18W/10/4P 1CT/25
Voltage (Nom)	58 V	EAN/UPC - Case	8711500260192
Voltage (Nom)	58 V		


Actinic BL PL-S/PL-L

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 18W/10/4P 1CT/25	18 mm	39 mm	194.2 mm	220 mm	226.6 mm

Photometric data



Spectral Power Distribution Colour - PL-L 18W/10/4P 1CT/25

