

Membro degli Accordi di Mutuo Riconoscimento EA, IAF e ILAC Signatory of EA, IAF and ILAC Mutual Recognition Agreements





EU Type Examination Certificate

Date: 2021/01/18 n. **860210304/TE** Validity: 2026/01/17

This Certificate is a translation in English of the original Certificate issued in Italian.

The hereunder described items of Personal Protective Equipm<mark>ent</mark> have overcome positively the "EU type examination" (Module B), proving their conformity to the safety and health requirements of the Regulation (EU) 2016/425 (Annex II)

Manufacturer: (Responsible of the PPE)	U-GROUP SRL Via Borgomanero, 50 – 28040 Paruzzaro (NO) – Italia
Type of PPE:	Safety footwear in conformity with EN ISO 20345:2011 class I (= footwear in leather and other materials)
Category of PPE:	II: "medium" risks. This certificate is based on reference standards listed below: its validity is no longer ensured should new version of the standards come into force.

Model "NERO ESD" code RI20154

Description: <u>model</u>: A (low footwear);

fastening system: by means of laces;

processing: direct injection;

outsole: forma 7466 NIC with grey compact PU marked "ANTISTATIC OIL RESISTANT"

(CH00116);

midsole: black foam PU (CH00117);

<u>upper</u>: black grain leather Dollarino declared water-resistant and declared thickness 1,8/2,0 mm (PL00107) with retro-reflective insert LUXOR ARGENTO ECO (S100245) in the

heel;

collar: black fabric ALBANY coupled with PE (\$100047);

tongue: black fabric ALBANY semplice (S100046), centrally lined and padded;

bellows: black coated synthetic fabric SPICE (S100002);

vamp lining: grey three-dimensional knitting IMOLA coupled with black canvas (\$100649);

guarter and tongue lining: black three-dimensional knitting SURF (S100466);

<u>insole:</u> white multi-layered fabric with black print declared conductive art. WB FLEX (\$P00007), which also serves as penetration resistant insert;

<u>removable insock</u>: grey perforated foam material with white central insert in the rear zone, coupled with fluo green fabric with metallic wires and four grey foam outflows in the bending area (TL00162);

toecap: polimeric material, article PS240 HAWAI (PU00042).

Optional interchangeable orthopedic insocks (**DGUV 112-191**) described by the Customer as follows (see also page 3): SECOSOL® by Matthias Hartmann Orthopädie +

Sport GmbH (max thickness in the toetip area: 2,9 mm): SECOSOL® COMPLETE – article number 951622012451XX

SECOSOL® LAMINATO CON TESSUTO – article number 9516101XXX7XXX

Technical Standard: EN ISO 20344:2011 Personal protective equipment – Test methods for footwear

(UNI EN ISO 20344:2012) **EN ISO 20345:2011**(UNI EN ISO 20345:2012)

Personal protective 6

Personal protective equipment – Safety footwear

Intended use: general industry, engineering industry, agriculture, warehouses, works on trucks, cranes.

STATE SAMPLES TO STATE OF THE S



DBD No 0330 E

Membro degli Accordi di Mutuo Riconoscimento EA, IAF e ILAC Signatory of EA, IAF and ILAC Mutual Recognition Agreements





EU Type Examination Certificate

Date: 2021/01/18 n. **860210304/TE** Validity: 2026/01/17

Size range: from 35 to 48

Technical File: DC-12807/E

Test report: RCT n°4030110

Functions and performance levels:

basic requirements for safety footwear (SB) (see Table 2 and 3 of EN ISO 20345:2011): all mandatory ones, among which:

SRC = Slip resistance – meets the following requirement:

- <u>surface</u>: ceramic / <u>lubricant</u>: detergent solution;
- surface: steel / <u>lubricant</u>: glycerol.

Additional requirements (Tab. 18 and 20 of EN ISO 20345:2011):

S3 = closed seat region, antistatic properties, energy absorption of seat region, resistance to fuel oil, water penetration resistance and absorption (water-repellent upper), penetration resistance, cleated outsole; **C1 =** cold insulation of the sole complex.

Note 1: the penetration resistance of the synthetic stitch proof insole tends to decrease with the diameter of the perforating object; in return the synthetic insole offers more protective surface and ergonomics advantages (flexibility, insulation, humidity and impact absorption).

Note 2: the footwear also meets the requirement in accordance with IEC 61340-5-1:2016 (IEC 61340-4-3:2017) for the electrical resistance **ESD** (electric dissipative footwear.

Marking:

on a stitched label and displaying the following information:

- CE Marking;
- registered trademark, name and complete address of the Manufacturer;
- designation of the footwear (= article name and alphanumeric code);
- nr. and year of the Standard of reference + safety symbols;
- size of the footwear (printed on the outsole);
- production date (month + year);
- additional information: website, category of the PPE, "Made in ...".





DBD No USSU B

Membro degli Accordi di Mutuo Riconoscimento EA, IAF e ILAC Signatory of EA, IAF and ILAC Mutual Recognition Agreements





EU Type Examination Certificate

Date: 2021/01/18 n. **860210304/TE** Validity: 2026/01/17



www.u-power.it

UGROUP RI20154

10/2020 NERO ESD

EN ISO 20345:2011 S3 CI SRC ESD

MADE IN TUNISIA

UGROUP SRL Via Borgomanero,50 Paruzzaro (NO)-Italy

DPI II



SECOSOL® COMPLETE 951622012451XX



SECOSOL® LAMINATO CON TESSUTO 9516101XXX7XXX



NOTE: the Technical File contains a more detailed description of the PPE (material, method of assembly, photographs or drawings), performance data, safety functions and level of protection, elements of conformity to the basic and supplementary requirements.

The Technical File is integral part of the present Certification, which has to be kept available by the applicant to be forwarded - upon request - to the entitled person (supervising body, Controlling Officer).

